



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 885TRGRY Radiant 15A/125V TR Duplex Recept Gy

*Pass & Seymour/Legrand*

Catalog Number	885TRGRY
Manufacturer	Pass & Seymour/Legrand
Description	Take A Step Up From The Standard. This Tamper-Resistant Duplex Outlet Installs Easily For The Basic Power Every Home Needs, While Elevating Your Space With The Sleek, Clean Lines Of Radiant® For A Sophisticated Look. Made Exclusively For Use With Screwless Wall Plates From The Radiant® Collection, Sold Separately.
Weight per unit	0.1386 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

gang	2
indoor/outdoor	Indoor
insulation	False
Mounting Type	Box
orientation	Vertical
Outlet Type	Tamper-Resistant
Poles	2
Voltage	125.0 V

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	4.25"
Thickness	1.3"

### Descriptions

Description	RADIANT 15A/125V TR DUPLEX RECP GY
extra long description	P&S 885TRGRY RADIANT 15A/125V TR DU
Long Description	Take a step up from the standard. This tamper-resistant duplex outlet installs easily for the basic power every home needs, while elevating your space with the sleek, clean lines of radiant® for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.
Product Type	Radiant 15A/125V TR Dup Recep Gry
Special Features	Tamper resistant, protects children, extra long strap, high impact resistant construction, quick loop wire aid



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007240504
Manufacturers Part Number	885-TRGRY
UPC	785007240504

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	10
Package	200
Weight Per each	0.1386

## Uses, Certifications, and Standards

Application	Residential/Commercial
environmental conditions	95% (relative humidity, non-condensing)
Mounting	WALL
nema rating	15A
standard	CULUS, UL, UL 498