



Catalog Number: 8860-GHC1-NK
Item Description: N1 HINGE CVR GUTTER NK
UPC Code: 784572109612

Brand Name: Milbank
Type: Lay In Wireway
Application: Wireway
Standard: UL Listed, Type 1
Cover Type: Hinge Cover
Enclosure: Indoor Enclosure
Nominal Cross Section: 8x8
Straight Section Length: 60
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: False






Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

| CATALOG# | LABEL# |
|-----------------|---------|
| 8860-GHC1(-) | 1002943 |
| RC-8860-GHC1(-) | 1125051 |
| SPH-885(-) | 1132575 |

| ITEM | QTY. | PART NUMBER | DESCRIPTION |
|------|------|-------------|---------------------|
| 1 | 1 | (SEE CHART) | BACK |
| 2 | 1 | (SEE CHART) | TOP |
| 3 | 5 | 1003198 | HINGE |
| 4 | 7 | 1001290 | SCREW, 10-32 X 5/16 |
| 5 | 1 | (SEE CHART) | LABEL (U/L LISTING) |
| 6 | 1 | 1002913 | LABEL, RATING |
| 7 | 3 | 1002880 | BAG ASSY. |



| SUFFIX | BACK # | COVER # |
|--------|---------|---------|
| -SU | 1105225 | 1002287 |
| -SUC | 1129003 | 1128967 |
| -SO | 1129004 | 1128968 |
| -SUNK | 1100202 | 1002287 |
| -NK | 1129005 | 1128968 |
| -SUNKC | 1129006 | 1128967 |



| SUFFIX | FINISH |
|--------|-------------|
| NONE | PAINTED |
| -NP | NOT PAINTED |

NOTE:
1. PLACE BAG ASS'Y INSIDE ENCLOSURE. (NOT SHOWN)

| REV | DATE | DESCRIPTION | BY | DL |
|-----|---------|---|-----|----|
| D | 8-29-07 | ADDED BACK & COVER CHART ECO. 15946 | | |
| D1 | 4/16/08 | ADDED LABEL CHART & REMOVED NOTE#2(ECO.17139) | JLT | |

| | | | |
|--|--------------------|---|---|
| Material: | 14 GA. - SEE CHART |  <p>General Offices: Kansas City, MO</p> | |
| Shear/ Die#: | | | |
| Finish: | SEE CHART | Title: | HINGE COVER WIREWAY 8 x 8 x 60, TYPE 1 NEMA ENCLOSURE |
| Part Wt.: | | Catalog No.: | (SEE CHART) |
| Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X* ±2* | | Customer: | MILBANK STANDARD |
| Third Angle  | | Drawing No.: | 365-11 |
| Scale: | NTS | Date: | 05/29/02 |
| Checked By: | | Sheet | 1 of 1 |
| Drawn By: | DY | Approved By: | |