




Catalog Number: 8872-GHC1-NK
Item Description: N1 HINGE CVR GUTTER NK
UPC Code: 784572289475

Brand Name: Milbank
Type: Lay In Wireway
Application: Wireway
Standard: UL Listed, Type 1
Cover Type: Hinge Cover
Enclosure: Indoor Enclosure
Nominal Cross Section: 8x8
Straight Section Length: 72
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: False





Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

| ITEM | QTY. | PART NUMBER | DESCRIPTION |
|------|------|-------------|---------------------|
| 1 | 1 | (SEE CHART) | BACK |
| 2 | 2 | (SEE CHART) | TOP |
| 3 | 6 | 1003198 | HINGE |
| 4 | 10 | 1001290 | SCREW, 10-32 X 5/16 |
| 5 | 1 | 1002943 | LABEL (U/L LISTING) |
| 6 | 1 | 1002913 | LABEL, RATING |
| 7 | 3 | 1002880 | BAG ASSY. |



| SUFFIX | BACK # | COVER # |
|--------|---------|---------|
| -SU | 1115846 | 1115847 |
| -SUC | 1129007 | 1128974 |
| -SO | 1129008 | 1128975 |
| -SUNK | 1117650 | 1115847 |
| -NK | 1129009 | 1128975 |
| -SUNKC | 1129010 | 1128974 |





- 3/4, 1 CONC. K.O.
32 PL
- 1/2, 3/4 CONC. K.O.
32 PL
- 1, 1-1/4 CONC. K.O.
8 PL

| SUFFIX | FINISH |
|--------|-------------|
| NONE | PAINTED |
| -NP | NOT PAINTED |

NOTE:
 1. PLACE BAG ASS'Y INSIDE ENCLOSURE. (NOT SHOWN)
 2. WHEN SOLD AS (RC)- PREFIX USE LABEL #1125051 INSTEAD OF #1002943

| REV. | DATE | DESCRIPTION | BY |
|------|---------|---|----|
| A | 8-29-07 | ADDED BACK & COVER CHART & REMOVED IT. 1115847 & ADDED 1128971 & IT. 1001290 QTY. W 12 ECO. 15946 | DL |

| | | |
|--|--------------------|--|
| Material: | 14 GA. - SEE CHART |  General Offices: Kansas City, MO |
| Shear/ Die#: | | |
| Finish: | SEE CHART | |
| Part Wt.: | | |
| Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X* ±2* | | Title: HINGE COVER WIREWAY 8 x 8 x 72, TYPE 1 NEMA ENCLOSURE Catalog No.: 8872-GHC1 Customer: MILBANK STANDARD Drawing No.: 11536-11 |
| Scale: | NTS | Third Angle  |
| Drawn By: | DY | Checked By: Approved By: |
| Date: | 05/29/02 | Sheet 1 of 1 |




Catalog Number: 8872-GHC1-NK
Item Description: N1 HINGE CVR GUTTER NK
UPC Code: 784572289475

Brand Name: Milbank
Type: Lay In Wireway
Application: Wireway
Standard: UL Listed, Type 1
Cover Type: Hinge Cover
Enclosure: Indoor Enclosure
Nominal Cross Section: 8x8
Straight Section Length: 72
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: False





Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

| ITEM | QTY. | PART NUMBER | DESCRIPTION |
|------|------|-------------|---------------------|
| 1 | 1 | (SEE CHART) | BACK |
| 2 | 2 | (SEE CHART) | TOP |
| 3 | 6 | 1003198 | HINGE |
| 4 | 10 | 1001290 | SCREW, 10-32 X 5/16 |
| 5 | 1 | 1002943 | LABEL (U/L LISTING) |
| 6 | 1 | 1002913 | LABEL, RATING |
| 7 | 3 | 1002880 | BAG ASSY. |



| SUFFIX | BACK # | COVER # |
|--------|---------|---------|
| -SU | 1115846 | 1115847 |
| -SUC | 1129007 | 1128974 |
| -SO | 1129008 | 1128975 |
| -SUNK | 1117650 | 1115847 |
| -NK | 1129009 | 1128975 |
| -SUNKC | 1129010 | 1128974 |





- 3/4, 1 CONC. K.O.
32 PL
- 1/2, 3/4 CONC. K.O.
32 PL
- 1, 1-1/4 CONC. K.O.
8 PL

| SUFFIX | FINISH |
|--------|-------------|
| NONE | PAINTED |
| -NP | NOT PAINTED |

NOTE:
 1. PLACE BAG ASS'Y INSIDE ENCLOSURE. (NOT SHOWN)
 2. WHEN SOLD AS (RC)- PREFIX USE LABEL #1125051 INSTEAD OF #1002943

| REV. | DATE | DESCRIPTION | BY | DL |
|------|---------|---|----|----|
| A | 8-29-07 | ADDED BACK & COVER CHART & REMOVED IT. 1115847 & ADDED 1128971 & IT. 1001290 QTY. W 12 ECO. 15946 | | |

| | | |
|--|--------------------|---|
| Material: | 14 GA. - SEE CHART |  General Offices: Kansas City, MO |
| Shear/ Die#: | | |
| Finish: | SEE CHART | |
| Part Wt.: | | |
| Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X* ±2* | | Third Angle  |
| Scale: | NTS | Checked By: |
| Drawn By: | DY | Approved By: |
| Title: | | HINGE COVER WIREWAY 8 x 8 x 72, TYPE 1 NEMA ENCLOSURE |
| Catalog No.: | | 8872-GHC1 |
| Customer: | | MILBANK STANDARD |
| Drawing No.: | | 11536-11 |
| Date: | 05/29/02 | Sheet 1 of 1 |