



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



884SC1NK Nema 1 SCR CVR Box No *Milbank*

| | |
|------------------|--|
| Catalog Number | 884SC1NK |
| Manufacturer | Milbank |
| Description | 8X4X8 Screw Cover Type 1 UI Listed Steel No Knockouts Ansi 61 Gray Cover With Teardrop Slots Mounting Holes In Back |
| Weight per unit | 5.0 (lbs/each) |
| Product Category | Nema Type 1 Metallic Enclosure |

Features

| | |
|------------------|------------------------|
| Cable Entry | No Knockouts |
| number of outlet | 0 |
| Support | Formed and Spot Welded |

Material, Color, and Finish

| | |
|-------|------|
| Color | Gray |
|-------|------|

Dimensions and Weight

| | |
|------|--------------|
| Size | 4L x 8W x 8H |
|------|--------------|

Descriptions

| | |
|------------------------|--|
| Construction | Welded |
| Description | NEMA 1 SCR CVR BOX NO |
| extra long description | MILB 884-SC1-NK N1 SCREW COVER ENCL |
| Long Description | 8x4x8 Screw Cover Type 1 UL Listed Steel No Knockouts ANSI 61 Gray Cover with Teardrop Slots Mounting Holes in Back |
| Product Type | N1 Screw Cover Encl NK 10940 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | MILBANK |
| GTIN | 00784572109407 |
| Manufacturers Part Number | 884-SC1-NK |
| UPC | 784572109407 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------|
| Category Description | STEEL WIRE WAY JUNCTION BOXES |
| Type | Screw Cover |

Packaging

| | |
|-----------------|---|
| Carton | 1 |
| Weight Per each | 5 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|---|
| Application | Enclosure for Mounting Electrical Equipment |
| Mounting | WALL MOUNT |
| standard | UL Listed |