

# Line Cord Switches

## Rotary Switches

### SPT-1



- 90-500 White
- 90-506 Brown
- 90-814 Black
- 90-2587 Ivory
- 90-2424 Gold
- 90-2425 Silver

On-Off Cord Switch for  
18/2 SPT-1  
6A-125V, 3A-250V, 3A-120V, 3A-125V

### SPT-2



- 90-573 White
- 90-574 Brown
- 90-825 Black
- 90-2629 Ivory
- 90-2426 Gold
- 90-2427 Silver

On-Off Cord Switch for  
18/2 SPT-2  
6A-125V, 3A-250V, 3A-120V, 3A-125V

### Hi-Low SPT-1



- 90-436 White
  - 90-435 Brown
  - 80-2231 Black
  - 80-2336 Ivory
- 200 Watt Hi-Low Dimmer for  
18/2 SPT-1  
200W-120V

### Hi-Low SPT-2



- 90-820 White
  - 90-821 Brown
  - 80-2232 Black
  - 80-2337 Ivory
- 200 Watt Hi-Low Dimmer for  
18/2 SPT-2  
200W-120V

## Rocker Switches

### SPT-2



- 90-2368 Black
- 90-2369 White
- 90-2370 Brown
- 90-2371 Silver
- 90-2372 Gold

Feed Thru Rocker Switch for  
18/2 SPT-2, 3A-120V

### SPT-1 / SPT-2 / SVT



- 90-434 Ivory
- 90-433 Brown

Heavy Duty Rocker Switch for  
18/2 SPT-1 & SPT-2, 16/2 SPT-2 & 18/2 SVT,  
3A-125V, 1/2HP-125V  
(Hole Size .280)

# Line Cord Switches

## Rotary Switches

### SPT-1



- 90-500 White
- 90-506 Brown
- 90-814 Black
- 90-2587 Ivory
- 90-2424 Gold
- 90-2425 Silver

On-Off Cord Switch for  
18/2 SPT-1  
6A-125V, 3A-250V, 3A-120V, 3A-125V

### SPT-2



- 90-573 White
- 90-574 Brown
- 90-825 Black
- 90-2629 Ivory
- 90-2426 Gold
- 90-2427 Silver

On-Off Cord Switch for  
18/2 SPT-2  
6A-125V, 3A-250V, 3A-120V, 3A-125V

### Hi-Low SPT-1



- 90-436 White
  - 90-435 Brown
  - 80-2231 Black
  - 80-2336 Ivory
- 200 Watt Hi-Low Dimmer for  
18/2 SPT-1  
200W-120V

### Hi-Low SPT-2



- 90-820 White
  - 90-821 Brown
  - 80-2232 Black
  - 80-2337 Ivory
- 200 Watt Hi-Low Dimmer for  
18/2 SPT-2  
200W-120V

## Rocker Switches

### SPT-2



- 90-2368 Black
- 90-2369 White
- 90-2370 Brown
- 90-2371 Silver
- 90-2372 Gold

Feed Thru Rocker Switch for  
18/2 SPT-2, 3A-120V

### SPT-1 / SPT-2 / SVT



- 90-434 Ivory
- 90-433 Brown

Heavy Duty Rocker Switch for  
18/2 SPT-1 & SPT-2, 16/2 SPT-2 & 18/2 SVT,  
3A-125V, 1/2HP-125V  
(Hole Size .280)