



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **886SCNK 8X8X6 SC No Ko** *Unity MFG*

|                  |   |
|------------------|---|
| Catalog Number   | 886SCNK   |
| Manufacturer     | Unity MFG   |
| Description      | Unity 886SCNK Screw-On Cover Enclosure, 16 Ga Painted Low Carbon Steel, Screw Terminal Connection, Gunsmoke Gray Color, Construction: Formed From Code Gauge, Low Carbon Steel, Keyhole Slotted Cover Allows Plated Screws to Stay In Place, Surface Mounting, No Knockouts, Dimensions: 8 In Width X 6 In Depth X 8 In Height, Enclosure: Nema 1, IP30, C/Us UI 50 and UI 50E - Type 1: Intended For Indoor Use Primarily to Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, Csa C22.2 No. 40 Certifie |
| Weight per unit  | 5.0 (lbs/each)  |
| Product Category | Nema Type 1 Metallic Enclosure  |

### **Features**

|            |                  |
|------------|------------------|
| connection | Screw Terminal   |
| Knockouts  | NO               |
| Material   | Low-Carbon Steel |

### **Material, Color, and Finish**

|       |      |
|-------|------|
| Color | Gray |
|-------|------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Construction           | Formed From Code Gauge, Low Carbon Steel, Keyhole Slotted Cover Allows Plated Screws To Stay In Place   |
| Description            | 8X8X6 SC NO KO  |
| extra long description | UNT 886SCNK N1 SCREW COVER PULL BOX   |
| Long Description       | Unity 886SCNK Screw-On Cover Enclosure, 16 GA Painted Low Carbon Steel, Screw Terminal Connection, Gunsmoke Gray Color, Construction: Formed From Code Gauge, Low Carbon Steel, Keyhole Slotted Cover Allows Plated Screws To Stay In Place, Surface Mounting, No Knockouts, Dimensions: 8 IN Width X 6 IN Depth X 8 IN Height, Enclosure: NEMA 1, IP30, C/US UL 50 And UL 50E - Type 1: Intended For Indoor Use Primarily To Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, CSA C22.2 No. 40 Certifie |
| Product Type           | N1 Screw Cover Pull Box No K.O. Powder Coated   |
| Special Features       | Covers have keyhole slots which allow the plated screws to stay in place and make for easy installation; Embossed grounding provision on sizes up to 24 IN x 24 IN x 12 IN; Holes are incorporated into the back of enclosure for easy mounting; Cover is secured to the body with plated hex head combo screws; Protects against contact with enclosed equipment; Thermoset polyester powder coated over phosphatized surface finish; For use as junction and pull boxes   |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Unity          |
| GTIN                      | 00761515222928 |
| Manufacturers Part Number | 886SCNK        |
| UPC                       | 761515222928   |

## Taxonomies, Classifications, and Categories

|                      |                               |
|----------------------|-------------------------------|
| Category Description | STEEL WIRE WAY JUNCTION BOXES |
| Type                 | Screw-On Cover Enclosure      |

## Packaging

|                 |   |
|-----------------|---|
| Carton          | 1 |
| Weight Per each | 5 |

## Uses, Certifications, and Standards

|                   |   |
|-------------------|---|
| Mounting standard | SURFACE<br>C/US UL 50 And UL 50E - Type 1: Intended For Indoor Use Primarily To Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, CSA C22.2 No. 40 Certified, IEC 60529, RoHS Compliant |
|-------------------|---|