ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



9736SW8809 6' APPLIANCE CORD STRAIGHT

SOUTHWIRE COMPANY

Catalog Number	9736SW8809
Manufacturer	SOUTHWIRE COMPANY
Description	16/3 6' SPT-3 PWR SPLY S/P
Weight per unit	0.4480 (lbs/ft)
Product Category	Portable Cord Sets

Features

Conductor Size	16
Number Of Conductors	2
Resistance	-20 to +60 C
Voltage Rating	5 +/-1 mA
Amperage Rating	13
Connection	5-15P
Core	PVC
Media	Yes
Outside Diameter	0.089
Strands	26/30

Material, Color, and Finish

Color	PVC
Jacket Material	PVC

Dimensions and Weight

Length	6

Descriptions

Description	6' APPLIANCE CORD STRAIGHT
Long Description	16/3 6' SPT-3 PWR SPLY S/P
Product Type	Cord, Power Supply 16/3 6' SPT-3 S/P
Extra Long Description	SWC 9736SW8809 CORD, POWER SUPPLY 1

Manufacturer Information

Brand	Cables & Cords
	Southwire
GTIN	00029892097363
Manufacturers Part Number	9736SW8809
UPC	885800

Taxonomies, Classifications, and Categories

Category Description	CORD SETS [DRYER & RANGE CORDS & BOOSTER CABLES)
Type	Cord Set

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Packaging

Carton	25
Weight	0.448
Weight Per Each	0.4480 (lbs/ft)

Uses, Certifications, and Standards

Application	Extension Cord
Temperature Rating	-40 to + 60 C
Standard	UL817

PIGTAILS – POWER SUPPLY CORD SPT-3 STRAIGHT AND RIGHT ANGLE

Rated 125 Volt



APPLICATION

Southwire's SPT-3 Power Supply Cords (pigtails) can be used for general purpose use. For multiple uses and suitable for a replacement power cord for air conditioners, refrigerators, freezers, microwaves

CONSTRUCTION

- Southwire's SPT-3 Power Supply Cords (pigtails) are manufactured using bare flexible stranded copper conductors with grey PVC insulation
- Available with a straight plug or right angle plug. The other end will be split and stripped

SPECIFICATIONS:

- UL Listed (UL 817)
- NEMA 5-15P

Stock #	Description	AWG	#COND	Cord Length (Ft)	Volts	AMPS	WATT
9724SW8809	REPLCORD, 16/3 SPT-3 R/ANGLE 4' GRAY SW	16	3	4	125	13A	1625
9726SW8809	REPLCORD, 16/3 SPT-3 R/ANGLE 6' GRAY SW	16	3	6	125	13A	1625
9733SW8809	REPLCORD, 16/3 SPT-3 STRAIGHT 3' GRAY SW	16	3	3	125	13A	1625
9734SW8809	REPLCORD, 16/3 SPT-3 STRAIGHT 4' GRAY SW	16	3	4	125	13A	1625
9736SW8809	REPLCORD, 16/3 SPT-3 STRAIGHT 6' GRAY SW	16	3	6	125	13A	1625

Copyright © 2020 Southwire Company, LLC. All Rights Reserved