


# OCCUPANCY & VACANCY SENSORS & TIMERS



**Wall Box Timers** 125, 125-T, 250 & 277VAC, 60 Hz



**97015I**

## Applications

- Lighting
- Exhaust fans
- Whirlpools and spas
- Saunas
- Heating and heat lamps
- Ventilating and air conditioning

## Features

- Units with "Hold" feature may be turned counter-clockwise to hold the load on without timing function.
- Turning clockwise causes unit to time load off after desired time delay.
- Quiet operation.
- Time range from 5 minutes to 1 hour.
- Available with or without hold.
- Decorator styling.
- Easily installed.
- Large head screw terminals.
- Accurate to  $\pm 5$  percent.
- Motor rated.
- Energy saving.

CATALOG NUMBER	DESCRIPTION	TIME RANGE	COLOR
<b>DIGITAL TIMERS</b>			
97015I			Ivory
97015W	Timeout, No Hold	15 Minutes	White
97015LA			Light Almond
97030I			Ivory
97030W	Timeout, No Hold	30 Minutes	White
97030LA			Light Almond
97060I			Ivory
97060W	Timeout, No Hold	60 Minutes	White
97115I			Ivory
97115W	Timeout, With Hold	15 Minutes	White
97160I			Ivory
97160W	Timeout, With Hold	60 Minutes	White


CATALOG NUMBER	COLOR
<b>REPLACEMENT KNOBS (WITHOUT PLATE)</b>	
PS55A1	White
PS55B1	Ivory
PS55G1	Light Almond

	VAC	HP
<b>RATINGS</b>		
20 Amp	125	1
10 Amp	250	1
10 Amp	277	
7 Amp	125 Tungsten	

# OCCUPANCY & VACANCY SENSORS & TIMERS



**Wall Box Timers** 125, 125-T, 250 & 277VAC, 60 Hz



**97015I**

## Applications

- Lighting
- Exhaust fans
- Whirlpools and spas
- Saunas
- Heating and heat lamps
- Ventilating and air conditioning

## Features

- Units with "Hold" feature may be turned counter-clockwise to hold the load on without timing function.
- Turning clockwise causes unit to time load off after desired time delay.
- Quiet operation.
- Time range from 5 minutes to 1 hour.
- Available with or without hold.
- Decorator styling.
- Easily installed.
- Large head screw terminals.
- Accurate to  $\pm 5$  percent.
- Motor rated.
- Energy saving.

CATALOG NUMBER	DESCRIPTION	TIME RANGE	COLOR
<b>DIGITAL TIMERS</b>			
97015I			Ivory
97015W	Timeout, No Hold	15 Minutes	White
97015LA			Light Almond
97030I			Ivory
97030W	Timeout, No Hold	30 Minutes	White
97030LA			Light Almond
97060I			Ivory
97060W	Timeout, No Hold	60 Minutes	White
97115I			Ivory
97115W	Timeout, With Hold	15 Minutes	White
97160I			Ivory
97160W	Timeout, With Hold	60 Minutes	White

CATALOG NUMBER	COLOR
<b>REPLACEMENT KNOBS (WITHOUT PLATE)</b>	
PS55A1	White
PS55B1	Ivory
PS55G1	Light Almond

	VAC	HP
<b>RATINGS</b>		
20 Amp	125	1
10 Amp	250	1
10 Amp	277	
7 Amp	125 Tungsten	