



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **A2011062 E1049 Yel M Instr** *Crouse-Hinds*

|                  |                                                                                                                                                             |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | A2011062                                                                                                                                                    |
| Manufacturer     | Crouse-Hinds                                                                                                                                                |
| Description      | Eaton Crouse-Hinds Series Roughneck E1049 Plug Insulator, Up to 1135A Continuous, 313-777 Kcmil, Yellow, Hexagon Crimp or Solder, Male, Rubber, 1000 Vac/DC |
| Weight per unit  | 1.0 (lbs/each)                                                                                                                                              |
| Product Category | Racks, Brackets, & Insulators                                                                                                                               |

### **Features**

|            |                                    |
|------------|------------------------------------|
| dimensions | 11.0000 IN X 3.8500 IN X 3.3800 IN |
| Material   | Rubber                             |

### **Dimensions and Weight**

|      |                                   |
|------|-----------------------------------|
| Size | 3.00 In Diameter X 8.50 In Length |
|------|-----------------------------------|

### **Descriptions**

|                        |                                                                                                                                                                                                                                                                                                                                  |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | E1049 YEL M INSTR                                                                                                                                                                                                                                                                                                                |
| extra long description | CRS-H A201106-2 E1049 M P INS 313MC                                                                                                                                                                                                                                                                                              |
| Features               | Single conductor Roughneck high amperage connectors from Eaton's Crouse-Hinds Division are rugged and specifically designed for oil drilling applications. Weatherproof and providing a high level of indestructibility, the Roughneck connector offers the ultimate performance solution for safety and reliability challenges. |
| Long Description       | Eaton Crouse-Hinds series Roughneck E1049 plug insulator, Up to 1135A continuous, 313-777 kcmil, Yellow, Hexagon crimp or solder, Male, Rubber, 1000 Vac/dc                                                                                                                                                                      |
| Product Type           | E1049 M P Ins 313MCM to 777MCM YI                                                                                                                                                                                                                                                                                                |
| Special Features       | NEMA 3 Enclosure                                                                                                                                                                                                                                                                                                                 |

### **Manufacturer Information**

|                           |                           |
|---------------------------|---------------------------|
| Brand                     | EATON CROUSE-HINDS SERIES |
| GTIN                      | 00662275107299            |
| Manufacturers Part Number | A201106-2                 |
| UPC                       | 662275107299              |

### **Taxonomies, Classifications, and Categories**

|                      |                      |
|----------------------|----------------------|
| Category Description | Pin & Sleeve Devices |
| Type                 | Plug Insulator       |

### **Packaging**

|                 |   |
|-----------------|---|
| Carton          | 1 |
| Weight Per each | 1 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

|                          |                                                                       |
|--------------------------|-----------------------------------------------------------------------|
| Application              | Ind Facilities & Factories - Facility: Power Distribution and Control |
| environmental conditions | -40 To 125 Deg C                                                      |
| standard                 | UL (CANADA AND US)                                                    |