



Fittings and Brackets


Z Shape Fittings




CAT. NO. A209
For attaching "A" series channel.




CAT. NO. B209
For attaching "B" series channel.



CAT. NO. C209
For attaching "C" series channel.



CAT. NO. CZ209
For attaching "A" back to back.




CAT. NO. EZ209
For attaching "E" series channel.

..... Standard Dimensions


- Hole Spacing: 1 3/16" From End
- Hole Spacing: 1 7/8" Centers
- Hole Size: 1" Diameter
- Material: 1 1/8" Width
- Material: 1/4" Thick

Standard Finish — GoldGalv[®], unless otherwise stated.
Add EG suffix for SilverGalv[®] Finish


Wing Shape Fittings




CAT. NO. A217




CAT. NO. A218




CAT. NO. AW204




CAT. NO. AW205 L




CAT. NO. AW205-R




CAT. NO. AW214




CAT. NO. AW219




CAT. NO. AW220



CAT. NO. AW224



CAT. NO. AW226



CAT. NO. AW228


..... Standard Dimensions

- Hole Spacing: 1 3/16" From End
- Hole Spacing: 1 7/8" Centers
- Hole Size: 1" Diameter
- Material: 1 1/8" Width
- Material: 1/4" Thick


Standard Finish — GoldGalv[®], unless otherwise stated.
Add EG suffix for SilverGalv[®] Finish

Fittings and Brackets


Z Shape Fittings




CAT. NO. A209
For attaching "A" series channel.




CAT. NO. B209
For attaching "B" series channel.



CAT. NO. C209
For attaching "C" series channel.



CAT. NO. CZ209
For attaching "A" back to back.




CAT. NO. EZ209
For attaching "E" series channel.

..... Standard Dimensions


- Hole Spacing: 1 3/16" From End
- Hole Spacing: 1 7/8" Centers
- Hole Size: 1" Diameter
- Material: 1 1/8" Width
- Material: 1/4" Thick

Standard Finish — GoldGalv[®], unless otherwise stated.
Add EG suffix for SilverGalv[®] Finish


Wing Shape Fittings




CAT. NO. A217




CAT. NO. A218




CAT. NO. AW204




CAT. NO. AW205 L




CAT. NO. AW205-R




CAT. NO. AW214




CAT. NO. AW219




CAT. NO. AW220



CAT. NO. AW224



CAT. NO. AW226



CAT. NO. AW228

..... Standard Dimensions

- Hole Spacing: 1 3/16" From End
- Hole Spacing: 1 7/8" Centers
- Hole Size: 1" Diameter
- Material: 1 1/8" Width
- Material: 1/4" Thick

Standard Finish — GoldGalv[®], unless otherwise stated.
Add EG suffix for SilverGalv[®] Finish