



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A36H3612SSLP 36X36X12 SS J-Box

Hoffman Enclosures, Inc.

| | |
|------------------|---|
| Catalog Number | A36H3612SSLP |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Wallmount Hinged With Nema Clamps Type 4X, 36X36X12, Brushed, SS304 |
| Weight per unit | 103.0 (lbs/each) |
| Product Category | Nema Types 4 & 4X Metallic Enc |

Features

| | |
|-----------|---------------------|
| ip rating | IP66 |
| Material | Stainless Steel 304 |

Material, Color, and Finish

| | |
|--------|------------|
| Color | Unpainted |
| Finish | Brushed #4 |

Dimensions and Weight

| | |
|--------|----------------------|
| Depth | 12 |
| Height | 36 |
| Size | 36.00x36.00x12.00 in |
| Width | 36 |

Descriptions

| | |
|------------------------|--|
| Description | 36X36X12 SS J-BOX |
| extra long description | NVENT HOF A36H3612SSLP Stainless En |
| Features | For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants. |
| Long Description | Wallmount Hinged with NEMA Clamps Type 4X, 36x36x12, Brushed, SS304 |
| Product Type | Stainless Encl. 36.00X36.00X12 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510290702 |
| Manufacturers Part Number | A36H3612SSLP |
| UPC | 783510290702 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | STEEL JUNCTION BOXES |
| Type | Stainless Steel Wall Mounted Industrial Enclosures |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 103 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Corrosive Environments; Controls and Drives |
| nema rating | 4X Watertight, corrosion-resistant |