ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
600 E 23rd Street
66046-0000, KS Lawrence
Phone: 785-330-9441
Fax: 785-371-0291



# A101072RT 10X10X72 N3R WR TR

*Hoffman Enclosures, Inc.*

| | |
|---|---|
| Catalog Number | A101072RT |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Wiring Trough Nema Type 3R, 10.00X10.00X72.00, Gray, Steel |
| Weight per unit | 75.0 (lbs/each) |
| Product Category | Nema Type 3R Trough & Gutter |

## Features

| | |
|---|---|
| ip rating | IP32 |
| Material | Mild Steel;Steel |

## Material, Color, and Finish

| | |
|---|---|
| Color | Gray |
| Color Code | ANSI 61 |
| Finish | Galvanized |

## Dimensions and Weight

| | |
|---|---|
| Depth | 72 |
| Size | 10.00x10.00x72.00 in |
| Width | 10 |

## Descriptions

| | |
|---|---|
| Description | 10X10X72 N3R WR TR |
| extra long description | NVENT HOF A101072RT Wire Trough, Ty |
| Features | Screw-Cover Wiring Trough, Type 3R is used for protecting wire and cable distribution, junctions and terminations in outdoor applications that may be exposed to wet conditions. A Padlock Hasp Kit can be installed for increased security. |
| Long Description | Wiring Trough NEMA Type 3R, 10.00x10.00x72.00, Gray, Steel |
| Product Type | Wire Trough, Type 3R |
| Short Description | Wire Trough, Type 3R |

## Manufacturer Information

| | |
|---|---|
| Brand | Nvent Hoffman |
| GTIN | 00783510430399 |
| Manufacturers Part Number | A101072RT |
| UPC | 783510430399 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | STEEL WIRE WAY JUNCTION BOXES |
| Type | Commercial Wiring Troughs;Trough |

## Packaging

| | |
|---|---|
| Carton | 1 |
| Weight Per each | 75 |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
600 E 23rd Street
66046-0000, KS Lawrence
Phone: 785-330-9441
Fax: 785-371-0291

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | Power Distribution |
| nema rating | 3R Weather-resistant, except dust |