



Fittings and Brackets


U Shape Fittings




CAT. NO. A208
Does not include strut nut or bolts. For "A" series channel.




CAT. NO. A210
For attaching "A" series channel.




CAT. NO. A211
For attaching "A" series channel.




CAT. NO. B210




CAT. NO. AB245




CAT. NO. AN211




CAT. NO. A212




CAT. NO. AB-288



CAT. NO. A-213



CAT. NO. C210
For attaching "C" series channel.




CAT. NO. E210
For attaching "E" series channel.

Standard Dimensions


- Hole Spacing: 1 3/8" From End
- Hole Spacing: 1 7/8" Centers
- Hole Size: 1" Diameter
- Material: 1 5/8" Width
- Material: 1/4" Thick

Standard Finish – GoldGalv®, unless otherwise stated.
Add EG suffix for SilverGalv® Finish


Angular Fittings



CAT. NO. AB225



CAT. NO. AB227




CAT. NO. AB-239

CAT. NO.	A (IN.)	B (IN.)	STD. CTN.
AB239 1	7 13/16	8 1/2	15
AB-239-2	13 3/4	17	10
AB-239-3	19 3/4	25 1/2	10


Standard Finish – GoldGalv®, unless otherwise stated.
Add EG suffix for SilverGalv® Finish

Fittings and Brackets


U Shape Fittings




CAT. NO. A208
Does not include strut nut or bolts. For "A" series channel.




CAT. NO. A210
For attaching "A" series channel.




CAT. NO. A211
For attaching "A" series channel.




CAT. NO. B210




CAT. NO. AB245




CAT. NO. AN211




CAT. NO. A212




CAT. NO. AB-288



CAT. NO. A-213



CAT. NO. C210
For attaching "C" series channel.




CAT. NO. E210
For attaching "E" series channel.

Standard Dimensions


- Hole Spacing: 1 3/8" From End
- Hole Spacing: 1 1/2" Centers
- Hole Size: 1" Diameter
- Material: 1 3/8" Width
- Material: 1/4" Thick

Standard Finish – GoldGalv®, unless otherwise stated.
Add EG suffix for SilverGalv® Finish


Angular Fittings



CAT. NO. AB225



CAT. NO. AB227



CAT. NO. AB-239

CAT. NO.	A (IN.)	B (IN.)	STD. CTN.
AB239-1	7 13/16	8 1/2	15
AB-239-2	13 3/4	17	10
AB-239-3	19 3/4	25 1/2	10

Standard Finish – GoldGalv®, unless otherwise stated.
Add EG suffix for SilverGalv® Finish