



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AE110L 110 CFM 1.3 Sones Led Fan/Light

Broan/Nutone LLC

|                  |   |
|------------------|---|
| Catalog Number   | AE110L  |
| Manufacturer     | Broan/Nutone LLC  |
| Description      | Bath Fan and Light, Ceiling Type; 9-1/4 Inch Length X 10 Inch Width X 5-3/4 Inch Height Size; UL, Hvi Approval; 120 Volt At 60 Hertz Voltage Rating; 0.3 Amp Current Rating; Yes Lamp Included; Led Lamp Type; 11 Watt Lamp Wattage |
| Weight per unit  | 9.1 (lbs/each)  |
| Product Category | Exhaust Fans  |

### Features

|                  |  |
|------------------|--|
| Air Flow Rate    | 110 CFM                                |
| Current Rating   | 0.3 Amp                                |
| Duct Shape       | Round                                  |
| Duct Size        | 4 Inch Diameter                        |
| Grill Finish     | White Polymeric                        |
| Grill Shape      | Rectangular                            |
| Grill Size       | 11-3/4 Inch Length x 12-1/2 Inch Width |
| Housing Shape    | Rectangular                            |
| Lamp Included    | Yes                                    |
| Lamp Type        | LED                                    |
| Lamp Wattage     | 11 Watt                                |
| Sound Level      | 1.3 SONES                              |
| Ventilation Area | 105 Square Foot                        |
| Voltage Rating   | 120 Volt at 60 Hertz                   |

### Material, Color, and Finish

|                  |                                  |
|------------------|----------------------------------|
| Housing Material | Rugged 26 Gauge Galvanized Steel |
|------------------|----------------------------------|

### Dimensions and Weight

|      |   |
|------|---|
| Size | 9-1/4 Inch Length x 10 Inch Width x 5-3/4 Inch Height |
|------|---|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Additional Information | Power Rating 23.4 Watt; Number of Speed 1; Includes Permanently Lubricated Plug-In Motor, Tapered Sleeve, Non-Metallic Damper; Excludes Metallic Clatter; Standard Package 1 per pack   |
| Commodity Description  | Exhaust Fans  |
| Description            | 110 CFM 1.3 SONES LED FAN/LIGHT   |
| extra long description | CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT AT 60 HERTZ VOLTAGE RATING; 0.3 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 11 WATT LAMP WATTAGE; RUGGED 26 GAUGE GALVANIZED STEEL HOUSING MATERIAL; 110 CFM AIR FLOW RATE; 4 INCH DIAMETER DUCT SIZE; 1.3 SONES SOUND LEVEL; 11-3/4 INCH LENGTH X 12-1/2 INCH WIDTH GRILL SIZE; RECTANGULAR HOUSING SHAPE; ROUND DUCT SHAPE; RECTANGULAR GRILL SHAPE; WHITE POLYMERIC GRILL FINISH; 105 SQUARE FOOT VENTILATION |
| Long Description       | BATH FAN AND LIGHT, CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT AT 60 HERTZ VOLTAGE RATING; 0.3 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 11 WATT LAMP WATTAGE   |
| Product Type           | Bath Fan and Light  |

## Manufacturer Information

|                           |                  |
|---------------------------|------------------|
| Brand                     | Broan/Nutone LLC |
| GTIN                      | 00026715236664   |
| Manufacturers Part Number | AE110L           |
| UPC                       | 026715236664     |

## Taxonomies, Classifications, and Categories

|                      |                |
|----------------------|----------------|
| Category Description | FANS & HEATERS |
| Type                 | CEILING        |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 9.07 |

## Uses, Certifications, and Standards

|          |         |
|----------|---------|
| Approval | UL, HVI |
|----------|---------|