



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AFB0ELDDBTXDUVOL Led Egress Emgcy DRKBRZ

Lithonia Lighting - Acuity

Catalog Number	AFB0ELDDBTXDUVOL
Manufacturer	Lithonia Lighting - Acuity
Description	Affinity Basic, Normally Off With Internal Battery , Dark Bronze Textured, 120-347VAC, Sealed, Maintenance Free Nickel-Cadmium Battery, Wide Throw High
Weight per unit	4.0 (lbs/each)
Product Category	Lighting

Features

battery life	90 min
Fixture Type	Emergency Lighting Unit
Hardware	No
Lamp Included	Yes
Lamp Type	LED - Static
Lamp Wattage	3
lumens	225 LM
Material	Aluminum
Maximum Operating Temperature	50
Shape	Semi-Cylinder
Voltage Rating	120-277
Warranty	5
Wattage	3

Material, Color, and Finish

Color	Bronze
color temperature	4000
Finish	Textured
Lens Color	Clear
Lens Material	Acrylic

Descriptions

Construction	New Construction
Description	LED EGRESS EMGCY DRKBRZ
extra long description	LITH AFB OEL DDBTXD UVOLT N WT Basi
Long Description	Affinity Basic, Normally Off with internal battery , Dark bronze textured, 120-347VAC, Sealed, maintenance free nickel-cadmium battery, Wide Throw High
Product Type	Emergency Lighting Unit



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00193047923187
Manufacturers Part Number	AFB OEL DDBTXD UVOLT N WT
UPC	193047923187

Taxonomies, Classifications, and Categories

Category Description	Emergency & Exit Lighting
Type	Emergency Lighting Unit

Packaging

Carton	1
Weight Per each	4

Uses, Certifications, and Standards

Application	Education,Government,Healthcare,Hospitality,House of Worship,Offices & Banks,Retail
environmental conditions	OUTDOOR
Mounting	SURFACE
standard	C-UL-US,NFPA 101,NFPA 70,NOM,ULCA Title 20,ROHS