



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AH1223W SW TOGGLE3WAY 20A 120/277VAUTOGRD B&S WH

Eaton Wiring Devices

Catalog Number	AH1223W
Manufacturer	Eaton Wiring Devices
Description	Eaton Arrow Hart Industrial Grade Toggle Switch, #14-10 Awg, 20A, Industrial, Wall, 120/277V, Back and Side, Screw, White, Three-Way, Brass, Terminals: 0.031 In, Polycarbonate
Weight per unit	0.0010 (lbs/each)
Product Category	Disconnect Motor Switches

Features

amperage rating	20
dimensions	1.3000 IN X 1.0050 IN X 4.1900 IN
Material	Polycarbonate
media	Yes
Poles	1
Voltage Rating	120/277 V

Descriptions

Description	SW TOGGLE3WAY 20A 120/277VAUTOGRD B&S WH
extra long description	EWD AH1223W SW Toggle3Way 20A 120/2
Features	Eaton's Arrow Hart broad line of extra heavy-duty industrial grade switches feature superior engineering, reliable performance and ease of installation. Available in toggle, lighted, pilot light, Corbin and locking versions.
Long Description	Eaton Arrow Hart industrial grade toggle switch, #14-10 AWG, 20A, Industrial, Wall, 120/277V, Back and side, Screw, White, Three-Way, Brass, Terminals: 0.031 in, Polycarbonate
Product Type	SW TOGGLE3WAY 20A 120/277VAUTOGRD B&S WH
Special Features	Commercial Grade

Manufacturer Information

Brand	COOPER WIRING DEVICES
GTIN	00032664734861
Manufacturers Part Number	AH1223W
UPC	032664734861

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	Industrial grade toggle switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.001

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility - Other
standard	cULus Listed,NOM,Federal Specification Classification W-S-896E