



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AH430C12W Conn Pin&Sleeve 30A 125/250V 3P4W WT or *Eaton Wiring Devices*

Catalog Number	AH430C12W
Manufacturer	Eaton Wiring Devices
Description	Connector Pin and Sleeve 30 Amp 125/250 Volt 3 Pole 4 Wire WT Orange
Weight per unit	24.0 (lbs/each)
Product Category	Pin & Sleeve Devices

Features

amperage rating	30
connection	Pin & Sleeve
dimensions	10.3750 IN X 4.7500 IN X 4.8130 IN
Material	Nylon;Other
media	Yes
Phase	3
Poles	3
Voltage Rating	125/250V/AC
Wire Size	0.433-0.985

Material, Color, and Finish

Color	Blue & Gray
-------	-------------

Dimensions and Weight

Size	10.375 x 4.75 x 4.813
------	-----------------------

Descriptions

Description	CONN PIN&SLEEVE 30A 125/250V 3P4W WT OR
extra long description	CRS-H AH430C12W CONN PIN AND SLEEVE
Features	Eaton's Arrow Hart full line of pin and sleeve devices offer sturdy nylon construction, rugged design with corrosion resistant components for lasting electrical performance, and watertight sealing that provides IP69K protection so you can feel confident in even the most severe washdown environments.
Long Description	CONNECTOR PIN AND SLEEVE 30 AMP 125/250 VOLT 3 POLE 4 WIRE WT ORANGE
Product Type	Conn Pin and Sleeve 30A 125/250V 3P4W WT
Special Features	Watertight P&S connectors

Manufacturer Information

Brand	Eaton
GTIN	00326647327066
Manufacturers Part Number	AH430C12W
UPC	032664732706



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Pin and Sleeve connector

Packaging

Carton	1
Package	24
Weight Per each	24

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
environmental conditions	IP67 & IP69k
Mounting	Cable
standard	IEC, UL, CSA