



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AH430R12W Recp Pin&Sleeve 30A 125/250V 3P4W WT or *Eaton Wiring Devices*

| | |
|------------------|---|
| Catalog Number | AH430R12W |
| Manufacturer | Eaton Wiring Devices |
| Description | Eaton Arrow Hart Pin and Sleeve Receptacle, IP69K Rated, #10 -#2 Awg, 30A, Extra Heavy-Duty, 125/250V, Back Wire, Orange, Nickel Plated Brass, IP67, IP69K, Nylon, Three-Pole, Four-Wire, Grounding, AHBB30 Back Box Style, Female, Nylon |
| Weight per unit | 32.0 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|-----------------|-----------------------------------|
| amperage rating | 30 |
| connection | Pin & Sleeve |
| dimensions | 3.7500 IN X 4.2100 IN X 3.1250 IN |
| insulation | Nylon PA6-GF30FR (17) |
| Material | Nylon;Other |
| media | Yes |
| Phase | 3 |
| Poles | 3 |
| Voltage Rating | 125/250V/AC |

Material, Color, and Finish

| | |
|-------|-------------|
| Color | Blue & Gray |
|-------|-------------|

Dimensions and Weight

| | |
|------|----------------|
| Size | 5.5 x 4.75 x 5 |
|------|----------------|

Descriptions

| | |
|------------------------|--|
| Description | RECP PIN&SLEEVE 30A 125/250V 3P4W WT OR |
| extra long description | EWD AH430R12W Recp Pin&Sleeve 30A 1 |
| Features | Eaton's Arrow Hart full line of pin and sleeve devices offer sturdy nylon construction, rugged design with corrosion resistant components for lasting electrical performance, and watertight sealing that provides IP69K protection so you can feel confident in even the most severe washdown environments. |
| Long Description | Eaton Arrow Hart pin and sleeve receptacle, IP69K Rated, #10 -#2 AWG, 30A, Extra Heavy-Duty, 125/250V, Back wire, Orange, Nickel plated brass, IP67, IP69K, Nylon, Three-pole, Four-wire, grounding, AHBB30 Back box style, Female, Nylon |
| Product Type | Recp Pin&Sleeve 30A 125/250V 3P4W WT or |
| Special Features | Watertight P&S receptacles |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00032664731952 |
| Manufacturers Part Number | AH430R12W |
| UPC | 032664731952 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------|
| Category Description | Pin & Sleeve Devices |
| Type | Pin and Sleeve receptacle |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Package | 32 |
| Weight Per each | 32 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Ind Facilities & Factories - Facility: Power Distribution and Control |
| environmental conditions | IP67 & IP69k |
| Mounting | Flange Mount |
| standard | cRUus |
| Temperature Rating | Max. 30°C (86°F) after 50 cycles of overload @150% of rated current |