



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AHCL1130R CCL Recept 30A 250V 3PH 3P3W BL&BK *Eaton Wiring Devices*

Catalog Number	AHCL1130R
Manufacturer	Eaton Wiring Devices
Description	Eaton Arrow Hart Color Coded Locking Receptacle, #14-8 Awg, 30A, Industrial, 250 V, Back and Side, Blue, Black, Ultra Grip, Glass Filled Nylon, L11-30, Three-Pole, Three-Wire, Glass-Filled Nylon
Weight per unit	0.3300 (lbs/each)
Product Category	Wiring Devices

Features

dimensions	1.6200 IN X 1.0300 IN X 3.6400 IN
media	Yes

Descriptions

Description	CCL RECP 30A 250V 3PH 3P3W BL&BK
extra long description	EWD AHCL1130R CCL Recept 30A 250V 3PH
Features	Eaton's Arrow Hart color coded locking devices are an industry-first solution that adds six voltage rating color codes consistent with IEC 60309 standards to locking plugs, connectors, inlets, outlets and receptacles to provide you a quick, clear and easy way to identify your circuit voltage. Available in standard NEMA configurations for 20A and 30A applications, the devices ensure long-lasting, dependable service in the most demanding environments, are built with a contemporary flare and ergonomic design
Long Description	Eaton Arrow Hart Color Coded Locking Receptacle, #14-8 AWG, 30A, Industrial, 250 V, Back and Side, Blue, Black, Ultra grip, Glass filled Nylon, L11-30, Three-pole, Three-wire, Glass-filled Nylon
Product Type	CCL Recept 30A 250V 3PH 3P3W BL&BK

Manufacturer Information

Brand	Eaton
GTIN	00032664758492
Manufacturers Part Number	AHCL1130R
UPC	032664758492

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Color Coded Locking



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.33

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility - Other
standard	UL Listed,NOM,RoHS Compliant,NAFTA