



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2569 E. Hwy 97
78064-0000, TX Pleasanton
Phone: 830-569-3390
Fax: 830-569-3608



AMS2 2-14 Al/Cu Butt Splice *Burndy LLC*

Catalog Number	AMS2
Manufacturer	Burndy LLC
Description	Aluminum Mechanical Splice, 2-14 Awg, 3/8" Screw Dia, 2 Screws, Al/Cu Rated, Tin Plated.
Weight per unit	0.0400 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Conductor Size	14-2 AWG
Hex Size	Slot
Material	Aluminum
pallet quantity	11520

Dimensions and Weight

Size	1.59 in x 0.56 in x 0.79 in
------	-----------------------------

Descriptions

Description	2-14 AL/CU BUTT SPLICE
extra long description	BUR AMS2 2-14 DUAL RATED SPLICE
Long Description	Aluminum Mechanical Splice, 2-14 AWG, 3/8" Screw Dia, 2 Screws, Al/Cu Rated, Tin Plated.
Product Type	SPLICE REDUCER
Special Features	Features: All Splicer/Reducers Are Dual Rated For Use With Aluminum And Copper Conductors And Are Constructed From High Strength, Tin Plated Aluminum, PENTROX Oxide Inhibiting Joint Compounds Are Recommended For All Aluminum Applications, All Connectors Are Tin-Plated: Provide Low Contact Resistance And Prevents Galvanic Corrosion, Connectors Feature Rounded Bottoms: Facilitates Taping, Solid Center Barrier: Prevents Contact Of Dissimilar Metals, Large Screw Diameters: Ensures Greater Surface Contact With

Manufacturer Information

Brand	BURNDY
GTIN	00781810241004
Manufacturers Part Number	AMS2
UPC	781810241004

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	AMS, Dual Rated



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2569 E. Hwy 97
78064-0000, TX Pleasanton
Phone: 830-569-3390
Fax: 830-569-3608

Packaging

Carton	1
Package	10
Weight Per each	0.04

Uses, Certifications, and Standards

Application	For Use With Copper And Aluminum Conductors
standard	ANSI C119.4
Temperature Rating	194° F