



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AR347 30A Pin & Sleeve Recept 4W 4P 250VDC/600vac *Crouse-Hinds*

Catalog Number	AR347
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Arktite Ar Receptacle, 30A, Four-Wire, Four-Pole, 50-400 HZ, Style 1, Copper-Free Aluminum, Threaded Cap, 600 Vac/250 VDC
Weight per unit	0.5000 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	30
connection	Pressure, Crimp/Solder
dimensions	3.5600 IN X 3.3800 IN X 3.3800 IN
Poles	4
Voltage Rating	600 VAC AT 50 TO 400 HZ, 250 VDC
Wire Size	10 To 6 AWG (Building), 10 To 8 AWG (Extra Flex)

### Dimensions and Weight

Height	3-3/8
Width	3-3/8

### Descriptions

Description	30A PIN & SLEEVE RECPT 4W 4P 250VDC/600VAC
extra long description	CRS-H AR347 30A 4W4P ARKTE RCPT HOU
Features	Crouse-Hinds series Arktite plugs and receptacles are used to supply power to portable electrically operated devices, such as motor generator sets, compressors, heating and cooling units, welders, conveyors, lighting systems and similar equipment. Also used where temporary power is needed, such as at trailers, building units, heavy machinery or wherever electrical loads must be quickly disconnected from power source.
Long Description	Eaton Crouse-Hinds series Arktite AR receptacle, 30A, Four-wire, four-pole, 50-400 Hz, Style 1, Copper-free aluminum, Threaded cap, 600 Vac/250 Vdc
Product Type	30A 4W4P Arkte RCPT Hous THRD Cap
Special Features	Heavy-Duty, Watertight, Grounding Style 1, NEMA 4 Enclosure, Threaded Cap

### Manufacturer Information

Brand	Eaton
GTIN	00782274060408
Manufacturers Part Number	AR347
UPC	782274060408



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... Pin & Sleeve Devices

Type ..... RECEPTACLE

## Packaging

Carton ..... 1

Package ..... 2

Weight Per each ..... 0.5

## Uses, Certifications, and Standards

Application ..... Ind Facilities & Factories - Facility: Power Distribution and Control

standard ..... UL 1682, UL 1686, CSA C22.2, CE