



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1510 Interstate 30
75087-0000, TX Rockwall
Phone: 469-913-1945
Fax: 469-913-1946



ASC2T 2 Al/Cu Compression

Nsi Industries

Catalog Number	ASC2T
Manufacturer	Nsi Industries
Description	Dual Rated Aluminum Splice 2 Awg Dual Rated Aluminum Splices Are A Type Of Aluminum Compression Connector That Is Produced From High Conductivity Aluminum Tubing. Center Stop Assures Proper Cable Installation. Electro-Tin Plated For Corrosion Resistance. Color Coded and Marked With Die Index Information. Pre-Filled With Oxide Inhibitor and Capped With Color Coded Cap.
Weight per unit	0.0400 (lbs/each)
Product Category	Splicing & Terminating Kits

Features

Material	Aluminum
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Pink
Finish	Tin Plated Bronze

Dimensions and Weight

Size	L=2.37 - OD=.527 - ID=.307
------	----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1510 Interstate 30
75087-0000, TX Rockwall
Phone: 469-913-1945
Fax: 469-913-1946

Descriptions

Description	2 AL/CU COMPRESSION
extra long description	NSI ASC2T 2 AWG Aluminum Splice - D
Features	Dual Rated Aluminum Splice 2 AWG Dual Rated Aluminum Splices are a type of aluminum compression connector that is produced from high conductivity aluminum tubing. Center stop assures proper cable installation. Electro-tin plated for corrosion resistance. Color coded and marked with die index information. Pre-filled with oxide inhibitor and capped with color coded cap.
Long Description	Dual Rated Aluminum Splice 2 AWG Dual Rated Aluminum Splices are a type of aluminum compression connector that is produced from high conductivity aluminum tubing. Center stop assures proper cable installation. Electro-tin plated for corrosion resistance. Color coded and marked with die index information. Pre-filled with oxide inhibitor and capped with color coded cap.
Product Type	2 Awg Aluminum Splice - Dual Rated - Pink
Special Features	# 2 AWG (STR) - ALCU Splice

Manufacturer Information

Brand	NSi
GTIN	00662381032027
Manufacturers Part Number	ASC2T
UPC	662381032027

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel - ALCU Splice

Packaging

Carton	1
Weight Per each	0.04

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
standard	UL486A/B
Temperature Rating	90 C