ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



# B1B B-CAP WIRE CONNECTOR, MODEL B1 YELLOW, 500/BAG

*IDEAL*

| | |
|---|---|
| Catalog Number | B1B |
| Manufacturer | IDEAL |
| Description | Wire Connector, (2) #20 AWG Conductor Size, (3) #12 AWG Conductor Size, Yellow Insulation Color, +221 °F Operating Temperature, 2 to 6 Conductors, 600 V ac, 0.0034 lb |
| Weight per unit | 0.0030 (lbs/each) |
| Product Category | Electrical Fixture Conn ( Nuts |

## Features

| | |
|---|---|
| Material | Flame-retardant Polypropelene |
| Voltage Rating | 600 |

## Material, Color, and Finish

| | |
|---|---|
| Color | Yellow |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

## Descriptions

| | |
|---|---|
| Description | B-CAP WIRE CONNECTOR, MODEL B1 YELLOW, 500/BAG |
| Features | The B-CAP Wire Connector gets you in those hard-to reach spots comfortably, especially when you're retrofitting or updating. Slim, classic fins and an expanding interior spring give the B-CAP a secure grip with extra leverage, making it the most compact connector on the market for up to 5 #12 (Red Model B2).The unique, space-saving profile of the B-CAP makes it perfect for retrofit work and shallow boxes.The B-CAP also features a tough, flame-retardant shell that withstands environmental extremes with a de |
| Long Description | Buchanan, Wire Connector, B-CAP, Conductor Range: 22 - 10 AWG, 3/20 AWG Min, 3/12 AWG Max, Number Of Conductors: 2 to 6, Material: Flame-retardant Polypropelene, Color: Yellow, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: B1 |
| Product Type | B-Cap B1 Yellow, 500 Bag |
| Special Features | 1,000V Maximum In Fixtures And Signs;Deep Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection;Easily Removed For Repeat Usage On Same Size Or Larger Wire Combinations;Features: Classic Fin Design Provides Secure Grip For Extra Leverage On Maximum Wire Combinations;Green-B Designed For Making Ground Connections And Bonding Non-Metallic Sheathed Cable;Live-Action Spring Expands To Accept Wire Shape And Size No Pre-Twisting Required;Model Number: B1;Square-Wire Spring T |
| Extra Long Description | IDEAL B1-B B-CAP B1 YELLOW, 500 BAG |

## Manufacturer Information

| | |
|---|---|
| Brand | Buchanan |
| | Ideal Industries |
| GTIN | 00781789451923 |
| UPC | 783250 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | Datacom Wiring Devices and Accessories |

## Availability

| | |
|---|---|
| Minimum Qty | 500 |

## Packaging

| | |
|---|---|
| Carton | 500 |
| Package | 5000 |
| Weight Per Each | 0.0030 (lbs/each) |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | Insulating or Joining 1 or more conductors |
| Environmental Conditions | Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F) |
| Standard | CSA C22.2 #188, UL 486C Listed, RoHS |