



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## B2210PAZN BLTF 1" Zinc Plate Pre-Assembled Unv Pipe Clamp

*Cooper B-Line/Cable Tray*

Catalog Number	B2210PAZN
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Multi-Grip and Offset Pipe Clamp, 0.0677" H X 2.6250" L X 1.25" W, Stainless Steel Finish, Rigid Conduit or Pipe
Weight per unit	0.1300 (lbs/each)
Product Category	Channel & Strut Fittings

### Features

dimensions	2.6250 IN X 1.2500 IN X 0.0677 IN
Material	14 Gauge Low Carbon Steel

### Material, Color, and Finish

Finish	Pre-Galvanized
--------	----------------

### Dimensions and Weight

Size	1 in
------	------

### Descriptions

Construction	TWO PIECE
Description	BLTF 1" ZINC PLATE PRE-ASSEMBLED UNV PIPE CLAMP
extra long description	B-LINE B2210PAZN 1"-MULTI-GRIP PIPE
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series multi-grip and offset pipe clamp, 0.0677" H x 2.6250" L x 1.25" W, Stainless steel finish, Rigid conduit or pipe
Product Type	1"-Multi-Grip Pipe Clamp, Pre-Asm, Thinwall, Imc, Rigid, Z
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut, Pipe Range 1.125 To 1.375 In OD, Load Capacity 400 Lb Vertical, 50 Lb Transverse

### Manufacturer Information

Brand	Eaton
GTIN	00781011604349
Manufacturers Part Number	B2210PAZN
UPC	781011604349

### Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	Multi-grip and offset pipe clamp



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	100
Weight Per each	0.13

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting	CHANNEL
standard	Not Applicable