



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **B2529 RND FB, STL, Shal, Full Adj, BRS (MS90)** *Hubbell Wiring Devices*

Catalog Number	B2529
Manufacturer	Hubbell Wiring Devices
Description	Hubbell Wiring Device Kellems, Floor and Wall Boxes, Flush Concretefloor Box Series, Round, Stampedsteel, Shallow, Fully Adjustable, Brass
Weight per unit	2.3 (lbs/each)
Product Category	Floor Boxes & Accessories

### **Features**

Cable Entry	From Top
Knockouts	6)1/2", 4)3/4"
Material	GALVANIZED STAMPED STEEL
service	Single

### **Material, Color, and Finish**

Color	Brass Flange
-------	--------------

### **Dimensions and Weight**

Height	2.91
Length	6
Size	6 in x 4.81 in x 2.91 in
Width	4.81

### **Descriptions**

Construction	Fabricated
Description	RND FB, STL, SHAL, FULL ADJ, BRS (MS90)
extra long description	HWDK B2529 RND FB, STL, SHAL, FULL
Long Description	Hubbell Wiring Device Kellems, Floor and Wall Boxes, Flush ConcreteFloor Box Series, Round, StampedSteel, Shallow, Fully Adjustable, Brass
Product Type	RND FB, STL, Shal, Full Adj, BRS (MS90)
Special Features	Concentric Knock-Outs;Fully Adjustable, PreGalvanized Stamped Steel Box

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585101804
Manufacturers Part Number	B2529
series	Flush Round - B25 Series
UPC	783585101804



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Round Galvanized Stamped Steel Box

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Package	4
Weight Per each	2.25

## Uses, Certifications, and Standards

Application	Single Service In-Floor Delivery Systems
Mounting standard	Cast Into Concrete UL/CSA;UL514