Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

537 N 40th St
72762-0000, AR Springdale
Phone: 479-361-2266
Fax: 479-361-9188



B41 B-Cap Wire Connector, Model B4 Blue/Gray, 25/Box

Ideal

Catalog Number	B41
Manufacturer	Ideal
Description	Color: Blue/Gray, Buchanan, Wire Connector, B-Cap®, Conductor Range: 14 - 6 Awg, 2/12 Awg Min, 2/6 Awg Max, Number Of Conductors: 2 to 6, Material: Flame-Retardant Polypropelene, Voltage Rating: 600 V, Environmental Conditions: Tough, Ul 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: B4
Weight per unit	0.0180 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Flame-retardant Polypropelene
Voltage Rating	600

Material, Color, and Finish

Color	Blue/Gray

Descriptions

Description	B-CAP WIRE CONNECTOR, MODEL B4 BLUE/GRAY, 25/BOX
Features	The B-CAP Wire Connector gets you in those hard-to reach spots comfortably, especially when you’re retrofitting or updating. Slim, classic fins and an expanding interior spring give the B-CAP a secure grip with extra leverage, making it the most compact connector on the market for up to 5 #12 (Red Model B2).The unique, space-saving profile of the B-CAP makes it perfect for retrofit work and shallow boxes.The B-CAP also features a tough, flame-retardant shell that withstands environmental extremes with a de
Long Description	Color: Blue/Gray, Buchanan, Wire Connector, B-CAP®, Conductor Range: 14 - 6 AWG, 2/12 AWG Min, 2/6 AWG Max, Number Of Conductors: 2 to 6, Material: Flame-retardant Polypropelene, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: B4

Manufacturer Information

Brand	Buchanan
GTIN	00781789452036
UPC	781789452036

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
537 N 40th St
72762-0000, AR Springdale
Phone: 479-361-2266
Fax: 479-361-9188

Availability

Manufacturer Status	Inactive
minimum qty	25
Status	Inactive

Packaging

Carton	250
Weight Per each	0.018

Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS