

## CONDUCTOR SLEEVE, COPPER, TINNED, STRAIGHT, 1" X 0.031", 0.344" DIA

### CATALOG NUMBER

**B1332G**



### FEATURES

Used to adapt a limited range of smaller size cables to a larger size nVent ERICO Cadweld Mold

Provides strength and stability on finely-stranded copper conductors

### PRODUCT ATTRIBUTES

Material: Copper

Finish: Tinned

Type: Straight

Length (L): 1"

Thickness (T): 0.03"

Diameter (Ø): 0.34"

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction,

property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**

## CONDUCTOR SLEEVE, COPPER, TINNED, STRAIGHT, 1" X 0.031", 0.344" DIA

### CATALOG NUMBER

**B1332G**



### FEATURES

Used to adapt a limited range of smaller size cables to a larger size nVent ERICO Cadweld Mold

Provides strength and stability on finely-stranded copper conductors

### PRODUCT ATTRIBUTES

Material: Copper

Finish: Tinned

Type: Straight

Length (L): 1"

Thickness (T): 0.03"

Diameter (Ø): 0.34"

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction,

property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**