



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## B2009PASS6 BLTF 3/4" Pa SS6 Rigid Pipe Clamp

*Cooper B-Line/Cable Tray*

Catalog Number	B2009PASS6
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Pre-Assembled O.D. Pipe and Conduit Clamp, 0.0740" H X 2.6080" L X 1.25" W, Steel, Stainless Steel Type 316
Weight per unit	0.0015 (lbs/each)
Product Category	Channel & Strut Fittings

### Features

dimensions	2.6080 IN X 1.2500 IN X 0.0740 IN
Material	316 Stainless Steel

### Material, Color, and Finish

Finish	STAINLESS STEEL TYPE 316
--------	--------------------------

### Dimensions and Weight

Size	3/4 in
------	--------

### Descriptions

Construction	TWO PIECE
Description	BLTF 3/4" PA SS6 RIGID PIPE CLAMP
extra long description	B-LINE B2009PASS6 3/4" PIPE/CONDUIT
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series pre-assembled O.D. pipe and conduit clamp, 0.0740" H x 2.6080" L x 1.25" W, Steel, Stainless steel type 316
Product Type	3/4" Pipe/Conduit Clamp, Rigid, 3/4", Pre-Asm, SSL
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut

### Manufacturer Information

Brand	Eaton
GTIN	00782051144390
Manufacturers Part Number	B2009PASS6
UPC	782051144390

### Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	Pre-assembled O.D. pipe and conduit clamp

### Packaging

Carton	1
Weight Per each	0.0015



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting	CHANNEL
standard	Not Applicable