



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BAB1025 Type Bab Circuit BRKR, 1P, 25AMP, 40C, 120/240V, 10, 000 *Eaton Corp*

| | |
|------------------|---|
| Catalog Number | BAB1025 |
| Manufacturer | Eaton Corp |
| Description | Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, High Intensity Discharge, 25 A, 10 Kaic, Single-Pole, 120/240 V, Non-Interchangeable, Q7, Bab |
| Weight per unit | 0.3500 (lbs/each) |
| Product Category | 1 Pole Standard Trip Bolt-On |

Features

| | |
|------------------|-----------------------------------|
| dimensions | 4.0000 IN X 1.0000 IN X 5.0000 IN |
| interrupt rating | 10 |
| media | Yes |
| Poles | 1 |
| Voltage Rating | 120/240 V |

Descriptions

| | |
|------------------------|--|
| Description | TYPE BAB CIRCUIT BRKR,1P,25AMP,40C,120/240V,10,000 |
| extra long description | ETN BAB1025 BAB ,1P,25AMP,40C,120/2 |
| Features | Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs. |
| Long Description | Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,High intensity discharge,25 A,10 kAIC,Single-pole,120/240 V,Non-Interchangeable,Q7,BAB |
| Product Type | Bab , 1P, 25AMP, 40C, 120/240V, 10ka |
| Special Features | High intensity discharge |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton Corp |
| GTIN | 00786679301258 |
| Manufacturers Part Number | BAB1025 |
| UPC | 786679301258 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS |
| Type | Thermal magnetic circuit breakers |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.35 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Datacenters - IT Space: CI and Hyper Converged
Marine Vessels and Equipment - Marine Vessels and Equipment -
Other
Other Generation - Renewable Energy - Alternative
Energy Generation - Conventional Energy - Conventional
Energy Residential Bldgs & Facilities - Residential Bldgs & Facilities
- Other

standard

CSA Certified, UL Listed