



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BAB1050 Type Bab Circuit BRKR 1P, 50AMP 40C 120/240V 10, 000

Eaton Corp

Catalog Number	BAB1050
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, High Intensity Discharge, 50 A, 10 Kaic, Single-Pole, 120/240 V, Non-Interchangeable, Q7, Bab
Weight per unit	0.3500 (lbs/each)
Product Category	1 Pole Standard Trip Bolt-On

Features

dimensions	3.8000 IN X 1.2000 IN X 4.8000 IN
interrupt rating	10
media	Yes
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	TYPE BAB CIRCUIT BRKR 1P,50AMP 40C 120/240V 10,000
extra long description	ETN BAB1050 BAB, 1p, 50A, 120/240V,
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15-100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,High intensity discharge,50 A,10 kAIC,Single-pole,120/240 V,Non-Interchangeable,Q7,BAB
Product Type	Bab, 1P, 50A, 120/240V, 10kaic
Special Features	High intensity discharge

Manufacturer Information

Brand	Eaton Corp
GTIN	00786679301500
Manufacturers Part Number	BAB1050
UPC	786679301500

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	0.35



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Generation - Renewable Energy - Alternative

EnergyOtherGeneration - Conventional Energy - Conventional

EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine

Vessels and Equipment - Marine Vessels and Equipment -

OtherResidential Bldgs & Facilities - Residential Bldgs & Facilities -

Other

standard

UL Listed,CSA Certified