



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## B2016PASS4 BLTD 3-1/2" SS4 Pa Rigid Pipe Clamp

*Cooper B-Line/Cable Tray*

Catalog Number	B2016PASS4
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Pre-Assembled O.D. Pipe and Conduit Clamp, 0.1040" H X 6.1410" L X 1.25" W, Steel, Stainless Steel Type 304
Weight per unit	0.6100 (lbs/each)
Product Category	Channel & Strut Fittings

### Features

dimensions	6.1410 IN X 1.2500 IN X 0.1040 IN
Material	304 Stainless Steel

### Material, Color, and Finish

Finish	STAINLESS STEEL TYPE 304
--------	--------------------------

### Dimensions and Weight

Size	3-1/2 in
------	----------

### Descriptions

Construction	TWO PIECE
Description	BLTD 3-1/2" SS4 PA RIGID PIPE CLAMP
extra long description	B-LINE B2016PASS4 3 1/2" PIPE/CONDU
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series pre-assembled O.D. pipe and conduit clamp, 0.1040" H x 6.1410" L x 1.25" W, Steel, Stainless steel type 304
Product Type	3 1/2" Pipe/Conduit Clamp, Rigid, 3 1/2", Pre-Asm, SS
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut

### Manufacturer Information

Brand	Eaton
GTIN	00781011872014
Manufacturers Part Number	B2016PASS4
UPC	781011872014

### Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	Pre-assembled O.D. pipe and conduit clamp

### Packaging

Carton	1
Weight Per each	0.61



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting	CHANNEL
standard	Not Applicable