



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BAB2015 BRKR A 10 Ka Per Line Current Capacity. 145 VDC BR**

*Eaton Corp*

Catalog Number	BAB2015
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, Bolt-On Mounting, Switching Neutral, 15 A, 10 Kaic, Two-Pole, 120/240 V, Non-Interchangeable, Q7, Bab
Weight per unit	0.6500 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

### **Features**

dimensions	3.8000 IN X 2.1000 IN X 4.8000 IN
interrupt rating	10
Poles	2
Voltage Rating	120/240 V

### **Descriptions**

Description	BRKR A 10 KA PER LINE CURRENT CAPACITY. 145 VDC BR
extra long description	ETN BAB2015 15A, 2 pole circuit bre
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,Bolt-on mounting, Switching neutral,15 A,10 kAIC,Two-pole,120/240 V,Non-Interchangeable,Q7,BAB
Product Type	15A, 2 Pole Circuit Breaker, Pow-R-Line
Special Features	Bolt-on mountingSwitching neutral TORQUE 4-10 AWG 20 IN LBS8AWG 25 IN LBS6-4 AWG 27 IN LBS

### **Manufacturer Information**

Brand	Eaton Corp
GTIN	00786679302156
Manufacturers Part Number	BAB2015
UPC	786679302156

### **Taxonomies, Classifications, and Categories**

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	12
Weight Per each	0.65

## Uses, Certifications, and Standards

Application	OtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	UL Listed,CSA Certified