



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## B2017PAZN BLTF 4" Zinc Plate Pa Rigid Pipe Clamp

*Cooper B-Line/Cable Tray*

Catalog Number	B2017PAZN
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Pre-Assembled O.D. Pipe and Conduit Clamp, 0.0994" H X 6.7030" L X 1.25" W, Steel
Weight per unit	0.6800 (lbs/each)
Product Category	Channel & Strut Fittings

### Features

dimensions	6.7030 IN X 1.2500 IN X 0.0994 IN
Material	11 Gauge Low Carbon Steel

### Material, Color, and Finish

Finish	Zinc Plated
--------	-------------

### Dimensions and Weight

Size	4 in
------	------

### Descriptions

Construction	TWO PIECE
Description	BLTF 4" ZINC PLATE PA RIGID PIPE CLAMP
extra long description	B-LINE B2017PAZN 4" PIPE/CONDUIT CL
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series pre-assembled O.D. pipe and conduit clamp, 0.0994" H x 6.7030" L x 1.25" W, Steel
Product Type	4" Pipe/Conduit Clamp, Pre-Asm, Rigid, 4", ZN PLTD
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut

### Manufacturer Information

Brand	Eaton
GTIN	00781011611040
Manufacturers Part Number	B2017PAZN
UPC	781011611040

### Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	Pre-assembled O.D. pipe and conduit clamp

### Packaging

Carton	1
Package	40
Weight Per each	0.68



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /  
Institutional Buildings / Structures - Other

Mounting

CHANNEL

standard

Not Applicable