



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BAB2040H BAB2040H BRKR A**

*Eaton Corp*

|                  |   |
|------------------|---|
| Catalog Number   | BAB2040H  |
| Manufacturer     | Eaton Corp  |
| Description      | Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, 40 A, 10 Kaic, Two-Pole, 240 V, Interchangeable, Bab, Distribution Panels 240V (Three-Phase, Four-Wire Maximum), Four-Wire, Three-Phase |
| Weight per unit  | 9.0 (lbs/each)  |
| Product Category | 2 Pole Standard Trip Bolt-On  |

### **Features**

|                  |                                   |
|------------------|-----------------------------------|
| dimensions       | 3.0000 IN X 2.0000 IN X 3.5000 IN |
| interrupt rating | 10                                |
| media            | Yes                               |
| Poles            | 2                                 |
| Voltage Rating   | 240 V - 240 V                     |

### **Descriptions**

|                        |  |
|------------------------|--|
| Description            | BAB2040H BRKR A  |
| extra long description | ETN BAB2040H TYPE BAB 40A 2P 240VAC  |
| Features               | Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15-100A are HACR rated. Select from one-, two-, or three-pole designs. |
| Long Description       | Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,40 A,10 kAIC,Two-pole,240 V,Interchangeable,BAB,Distribution panels 240V (Three-phase, four-wire maximum),Four-wire,Three-phase  |
| Product Type           | Type Bab 40A 2P 240VAC Instant SWBD CB   |
| Special Features       | Bolt-on mounting   |

### **Manufacturer Information**

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00786679302422 |
| Manufacturers Part Number | BAB2040H       |
| UPC                       | 786679302422   |

### **Taxonomies, Classifications, and Categories**

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS        |
| Type                 | Thermal magnetic circuit breakers |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |   |
|-----------------|---|
| Carton          | 1 |
| Weight Per each | 9 |

## Uses, Certifications, and Standards

|             |  |
|-------------|--|
| Application | Generation - Renewable Energy - Alternative Energy<br>Datacenters - IT Space: CI and Hyper Converged<br>Other Generation - Conventional Energy - Conventional Energy<br>Marine Vessels and Equipment - Marine Vessels and Equipment - Other<br>Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other |
| standard    | UL Listed, CSA Certified   |