



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BAB2045 BAB2045 BRKR A Eaton Corp

Catalog Number	BAB2045
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, Bolt-On Mounting, 45 A, 10 Kaic, Two-Pole, 240 V, Non-Interchangeable, Q7, Bab
Weight per unit	0.6500 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

### Features

dimensions	2.5000 IN X 2.0000 IN X 3.5000 IN
interrupt rating	10
media	Yes
Poles	2
Voltage Rating	120/240 V

### Descriptions

Description	BAB2045 BRKR A
extra long description	ETN BAB2045 BAB BREAKER 2P 40A MAX
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,Bolt-on mounting,45 A,10 kAIC,Two-pole,240 V,Non-Interchangeable,Q7,BAB
Product Type	Bab Breaker 2P 40A Max 240V Max 10K Aic
Special Features	Bolt-on mounting

### Manufacturer Information

Brand	Eaton
GTIN	00786679302446
Manufacturers Part Number	BAB2045
UPC	786679302446

### Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

### Packaging

Carton	1
Weight Per each	0.65



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Datacenters - IT Space: CI and Hyper Converged  
Renewable Energy - Alternative Energy  
Energy - Conventional Energy  
Other Marine Vessels and Equipment - Marine Vessels and Equipment - Other  
Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other

standard

CSA Certified, UL Listed