



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



B2210PAZN BLTF 1" Zinc Plate Pre-Assembled Unv Pipe Clamp

Cooper B-Line/Cable Tray

Catalog Number	B2210PAZN
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Multi-Grip and Offset Pipe Clamp, 0.0677" H X 2.6250" L X 1.25" W, Stainless Steel Finish, Rigid Conduit or Pipe
Weight per unit	0.1300 (lbs/each)
Product Category	Channel & Strut Fittings

Features

dimensions	2.6250 IN X 1.2500 IN X 0.0677 IN
Material	14 Gauge Low Carbon Steel

Material, Color, and Finish

Finish	Pre-Galvanized
--------	----------------

Dimensions and Weight

Size	1 in
------	------

Descriptions

Construction	TWO PIECE
Description	BLTF 1" ZINC PLATE PRE-ASSEMBLED UNV PIPE CLAMP
extra long description	B-LINE B2210PAZN 1"-MULTI-GRIP PIPE
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series multi-grip and offset pipe clamp, 0.0677" H x 2.6250" L x 1.25" W, Stainless steel finish, Rigid conduit or pipe
Product Type	1"-Multi-Grip Pipe Clamp, Pre-Asm. Thinwall, Imc, Rigid, Z
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut, Pipe Range 1.125 To 1.375 In OD, Load Capacity 400 Lb Vertical, 50 Lb Transverse

Manufacturer Information

Brand	Eaton
GTIN	00781011604349
Manufacturers Part Number	B2210PAZN
UPC	781011604349

Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	Multi-grip and offset pipe clamp



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.13

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting	CHANNEL
standard	Not Applicable