



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

310 Interstate Blvd  
29615-0000, SC Greenville  
Phone: 864-735-7911  
Fax: 000-000-0000



## **BAB3060H BAB3060H BRKR A**

*Eaton Corp*

Catalog Number	BAB3060H
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, 60 A, 10 Kaic, Three-Pole, 240 V, Interchangeable, Bab, Distribution Panels 240V (Three-Phase, Four-Wire Maximum), Four-Wire, Three-Phase
Weight per unit	1.0 (lbs/each)
Product Category	3 Pole Standard Trip Bolt-On

### **Features**

dimensions	3.8000 IN X 3.2000 IN X 4.7000 IN
interrupt rating	10
media	Yes
Poles	Three-pole
Voltage Rating	240 V - 240 V

### **Descriptions**

Description	BAB3060H BRKR A
extra long description	ETN BAB3060H BAB3060H BRKR A
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15-100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,60 A,10 kAIC,Three-pole,240 V,Interchangeable,BAB,Distribution panels 240V (Three-phase, four-wire maximum),Four-wire,Three-phase
Product Type	BAB3060H BRKR A
Special Features	Bolt-on mounting

### **Manufacturer Information**

Brand	Eaton
GTIN	00786679303603
Manufacturers Part Number	BAB3060H
UPC	786679303603

### **Taxonomies, Classifications, and Categories**

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

310 Interstate Blvd  
29615-0000, SC Greenville  
Phone: 864-735-7911  
Fax: 000-000-0000

## Availability

Status ..... Inactive .....

## Packaging

Carton ..... 1 .....

Package ..... 8 .....

Weight Per each ..... 1 .....

## Uses, Certifications, and Standards

Application ..... Generation - Renewable Energy - Alternative  
EnergyOtherGeneration - Conventional Energy - Conventional  
EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine  
Vessels and Equipment - Marine Vessels and Equipment -  
OtherResidential Bldgs & Facilities - Residential Bldgs & Facilities -  
Other .....

standard ..... UL Listed,CSA Certified .....