

# Eaton BBS-15

Catalog Number: BBS-15

Eaton Bussmann series BBS fuse, 15 A, Non-indicating, Ferrule end x ferrule end, Consult factory, Nickel-plated brass endcaps, Standard, 48 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series BBS fuse	BBS-15
<b>UPC</b>	<b>EAN</b>
051712707527	5027590056915
<b>Product Length/Depth</b>	<b>Product Height</b>
0.41 in	1.38 in
<b>Product Width</b>	<b>Product Weight</b>
0.41 in	0.12 lb
<b>Warranty</b>	<b>Compliances</b>
Not Applicable	CE Marked

## Electrical rating

### Amperage Rating

15 A

### Interrupt rating

Consult factory

### Voltage rating

48 V

## Physical details

### Material

Nickel-plated brass endcaps

### Packaging type

Standard

## General information

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

### Special features

Silver-plated fuse caps

## Resources

### Catalogs

Bussmann series complete full line catalog no. 1007

### Multimedia

Bussmann series Fuseology

### Specifications and datasheets

Eaton Specification Sheet - BBS-15

### Technical data sheets

BBS-15~BUSS MIDGET FUSE FAST ACTING

### Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton BBS-15

Catalog Number: BBS-15

Eaton Bussmann series BBS fuse, 15 A, Non-indicating, Ferrule end x ferrule end, Consult factory, Nickel-plated brass endcaps, Standard, 48 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series BBS fuse	BBS-15
<b>UPC</b>	<b>EAN</b>
051712707527	5027590056915
<b>Product Length/Depth</b>	<b>Product Height</b>
0.41 in	1.38 in
<b>Product Width</b>	<b>Product Weight</b>
0.41 in	0.12 lb
<b>Warranty</b>	<b>Compliances</b>
Not Applicable	CE Marked

## Electrical rating

### Amperage Rating

15 A

### Interrupt rating

Consult factory

### Voltage rating

48 V

## Physical details

### Material

Nickel-plated brass endcaps

### Packaging type

Standard

## General information

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

### Special features

Silver-plated fuse caps

## Resources

### Catalogs

Bussmann series complete full line catalog no. 1007

### Multimedia

Bussmann series Fuseology

### Specifications and datasheets

Eaton Specification Sheet - BBS-15

### Technical data sheets

BBS-15~BUSS MIDGET FUSE FAST ACTING

### Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)