



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BC2SS10C Dome-Top® BC2S-S10-C Lock *Panduit Corporation*

Catalog Number	BC2SS10C
Manufacturer	Panduit Corporation
Description	The BC2S-S10-C Dome-Top® Barb Ty Clamp Tie, Features A Unique Patented Design With Its Round Smooth Edges. Paired With The Stainless-Steel Locking Barb, These Cable Ties Provide Consistent Performance, Reliability and Infinite Adjustability Through The Entire Bundle Range. Standard Cross Section, 8.5" (261MM) Length. Appropriate For Indoor Use, Made Of Nylon 6.6, Are Natural In Color and Come In Packages Of 100.
Weight per unit	0.4400 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	50

Dimensions and Weight

Length	8.5
--------	-----

Descriptions

Description	DOME-TOP® BC2S-S10-C LOCK
extra long description	PAN BC2S-S10-C Dome-Top® BC2S-S10-C
Long Description	The BC2S-S10-C Dome-Top® barb ty clamp tie, features a unique patented design with its round smooth edges. Paired with the stainless-steel locking barb, these cable ties provide consistent performance, reliability and infinite adjustability through the entire bundle range. Standard cross section, 8.5" (261mm) length. Appropriate for Indoor use, made of Nylon 6.6, are natural in color and come in packages of 100.
Product Type	Dome-Top® BC2S-S10-C Locking Clamp Barb Tie, PA6.6, M5, 8.5"
Special Features	Indoor

Manufacturer Information

Brand	Panduit®
GTIN	00074983523146
Manufacturers Part Number	BC2S-S10-C
UPC	074983523146

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Locking Clamp Tie



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	100
Package	1000
Weight Per each	0.44

Uses, Certifications, and Standards

Application	Used to secure a cable bundle to another surface such a control panel, wall or ceiling.
standard	UL 62275 Compliant (Type 2, 21), UL Listed (File #E56854)