



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9172 E Florentine Road Unit 9  
86314-0000, AZ Prescott Valley  
Phone: 928-356-1174  
Fax: 480-426-8084



## BAB1050 Type Bab Circuit BRKR 1P, 50AMP 40C 120/240V 10, 000

Eaton Corp

Catalog Number	BAB1050
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, High Intensity Discharge, 50 A, 10 Kaic, Single-Pole, 120/240 V, Non-Interchangeable, Q7, Bab
Weight per unit	0.3500 (lbs/each)
Product Category	1 Pole Standard Trip Bolt-On

### Features

dimensions	3.8000 IN X 1.2000 IN X 4.8000 IN
interrupt rating	10
media	Yes
Poles	Single-pole
Voltage Rating	120/240 V

### Descriptions

Description	TYPE BAB CIRCUIT BRKR 1P,50AMP 40C 120/240V 10,000
extra long description	ETN BAB1050 BAB, 1p, 50A, 120/240V,
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15-100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,High intensity discharge,50 A,10 kAIC,Single-pole,120/240 V,Non-Interchangeable,Q7,BAB
Product Type	Bab, 1P, 50A, 120/240V, 10kaic
Special Features	High intensity discharge

### Manufacturer Information

Brand	Eaton
GTIN	00786679301500
Manufacturers Part Number	BAB1050
UPC	786679301500

### Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

### Availability

Status	Inactive
--------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9172 E Florentine Road Unit 9  
86314-0000, AZ Prescott Valley  
Phone: 928-356-1174  
Fax: 480-426-8084

## Packaging

Carton	1
Package	24
Weight Per each	0.35

## Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative EnergyOtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	UL Listed,CSA Certified