



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8110 Anderson Road Suite 100  
33634-0000, FL Tampa  
Phone: 813-934-6264  
Fax: 000-000-0000



## **BAB2020 BRKR A BAB2020~1230C41G12~1230C41G02~BRKR A** *Eaton Corp*

Catalog Number	BAB2020
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, Bolt-On Mounting, Switching Neutral, 20 A, 10 Kaic, Two-Pole, 120/240 V, Non-Interchangeable, Q7, Bab
Weight per unit	1.0 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

### Features

dimensions	2.9060 IN X 2.0000 IN X 2.9060 IN
interrupt rating	10
Poles	2
Voltage Rating	120/240 V

### Descriptions

Description	BRKR A BAB2020~1230C41G12~1230C41G02~BRKR A
extra long description	ETN BAB2020 20A, 2 pole circuit bre
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,Bolt-on mounting, Switching neutral,20 A,10 kAIC,Two-pole,120/240 V,Non-Interchangeable,Q7,BAB
Product Type	20A, 2 Pole Circuit Breaker, Pow-R-Line
Special Features	Bolt-on mountingSwitching neutral

### Manufacturer Information

Brand	Eaton
GTIN	00786679302200
Manufacturers Part Number	BAB2020
UPC	786679302200

### Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

### Availability

Status	Inactive
--------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8110 Anderson Road Suite 100  
33634-0000, FL Tampa  
Phone: 813-934-6264  
Fax: 000-000-0000

## Packaging

Carton	1
Weight Per each	1.03

## Uses, Certifications, and Standards

Application	OtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Renewable Energy - Alternative EnergyResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	UL Listed,CSA Certified