



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BAB2020 BRKR A BAB2020~1230C41G12~1230C41G02~BRKR A** *Eaton Corp*

|                  |   |
|------------------|---|
| Catalog Number   | BAB2020   |
| Manufacturer     | Eaton Corp  |
| Description      | Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, Bolt-On Mounting, Switching Neutral, 20 A, 10 Kaic, Two-Pole, 120/240 V, Non-Interchangeable, Q7, Bab |
| Weight per unit  | 1.0 (lbs/each)  |
| Product Category | 2 Pole Standard Trip Bolt-On  |

### Features

|                  |                                   |
|------------------|-----------------------------------|
| dimensions       | 2.9060 IN X 2.0000 IN X 2.9060 IN |
| interrupt rating | 10                                |
| Poles            | 2                                 |
| Voltage Rating   | 120/240 V                         |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | BRKR A BAB2020~1230C41G12~1230C41G02~BRKR A  |
| extra long description | ETN BAB2020 20A, 2 pole circuit bre  |
| Features               | Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs. |
| Long Description       | Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,Bolt-on mounting, Switching neutral,20 A,10 kAIC,Two-pole,120/240 V,Non-Interchangeable,Q7,BAB   |
| Product Type           | 20A, 2 Pole Circuit Breaker, Pow-R-Line  |
| Special Features       | Bolt-on mountingSwitching neutral  |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00786679302200 |
| Manufacturers Part Number | BAB2020        |
| UPC                       | 786679302200   |

### Taxonomies, Classifications, and Categories

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS        |
| Type                 | Thermal magnetic circuit breakers |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 1.03 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

OtherGeneration - Conventional Energy - Conventional  
EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine  
Vessels and Equipment - Marine Vessels and Equipment -  
OtherGeneration - Renewable Energy - Alternative  
EnergyResidential Bldgs & Facilities - Residential Bldgs & Facilities  
- Other

standard

UL Listed,CSA Certified