



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BABF1020 Fire Alarm BRKR Per Nfpa 72

Eaton Corp

| | |
|------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | BABF1020 |
| Manufacturer | Eaton Corp |
| Description | Eaton Bab Thermal Magnetic Circuit Breaker, Classic Replacement Circuit Breaker, 15 A, 10 Kaic At 120/240 V, Single-Pole, 120/240 V, #14-8 Awg Cu/Al, BQL |
| Weight per unit | 0.3500 (lbs/each) |
| Product Category | On Circuit Breakers |

Features

| | |
|------------------|-----------------------------------|
| dimensions | 3.2500 IN X 0.8750 IN X 3.5000 IN |
| interrupt rating | 10 kAIC |
| media | Yes |
| Poles | Single-pole |
| Voltage Rating | 120/240 V |

Descriptions

| | |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | FIRE ALARM BRKR PER NFPA 72 |
| extra long description | ETN BABF1020 FIRE ALARM BREAKER PER |
| Features | Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs. |
| Long Description | Eaton BAB thermal magnetic circuit breaker, Classic replacement circuit breaker, 15 A, 10 kAIC at 120/240 V, Single-pole, 120/240 V, #14-8 AWG Cu/Al, BQL |
| Product Type | Fire Alarm Breaker Per Nfpa 72 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00786685405063 |
| Manufacturers Part Number | BABF1020 |
| UPC | 786685405063 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS |
| Type | Thermal magnetic circuit breakers |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.35 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Marine Vessels and Equipment - Marine Vessels and Equipment -
OtherOtherGeneration - Renewable Energy - Alternative
EnergyGeneration - Conventional Energy - Conventional
EnergyDatacenters - IT Space: CI and Hyper ConvergedResidential
Bldgs & Facilities - Residential Bldgs & Facilities - Other

standard

UL Listed,NFPA 72,HACR Rated