



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BK20GB306TRUSB Usb Plugmold 3' BLK

Wiremold/Legrand

Catalog Number	BK20GB306TRUSB
Manufacturer	Wiremold/Legrand
Description	The Wiremold 2000 Series Raceway Offers A Selection Of Steel, Aluminum, and Nonmetallic Raceways That Provide A Versatile Solution For Many Applications. Plugmold Sections Offer Single or Alternating Circuits, In Standard or Isolated Ground Receptacles. The Scuffcoat Finish Is Scratch Resistant and Protects Against Nicks and Chips While Preventing Color From Fading.
Weight per unit	2.0 (lbs/each)
Product Category	Plugmold, Outlet Strips, Power

Features

Enclosure Type	Steel
media	Yes
Voltage	125.0 V

Descriptions

Description	USB PLUGMOLD 3' BLK
extra long description	WM BK20GB306TRUSB USB PLUGMOLD 3FT
Long Description	The Wiremold 2000 Series raceway offers a selection of steel, aluminum, and nonmetallic raceways that provide a versatile solution for many applications. Plugmold sections offer single or alternating circuits, in standard or isolated ground receptacles. The ScuffCoat finish is scratch resistant and protects against nicks and chips while preventing color from fading.
Product Type	Usb Plugmold 3FT Black
Special Features	Provides a great solution for adding the convenience of multiple outlets and USB charging to work or living areas.

Manufacturer Information

Brand	WIREMOLD
GTIN	00786776182538
Manufacturers Part Number	BK20GB306TRUSB
UPC	786776182538

Taxonomies, Classifications, and Categories

Category Description	Panduit & Wiremold Metallic & Non-Metallic Raceways
Type	Plugmold

Trade Size

Amperage	20.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	2
Weight Per each	1.95

Uses, Certifications, and Standards

environmental conditions	Dry Interior Locations
standard	CULUS, ROHS, cULus Listed Multioutlet assemblies: File E15191 Guide PVGT. Meets Article 380 of NEC.