




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BGRAL0SWW2MV0LTP BGR Alo SWW2 Mvolt Per Dna M2

Lithonia Lighting - Acuity

Catalog Number	BGRAL0SWW2MV0LTP
Manufacturer	Lithonia Lighting - Acuity
Description	Barn Lights, Security Lights, Yard Lights... Call Them What You Will, But They Are Everywhere! Despite Their Utilitarian Style and Simplistic Performance, They Pose A Significant Opportunity For An Upgrade to Led Lighting. The Lithonia Lighting® Barnguard Led Security Light Has It All With Its White Light, High Cri, Instant-On, and Low Energy Consumption. Adjustable Light Output Of Up to 10, 000 Lumens and Switchable Color Temperatures Are Standard Features Included. Barnguard Led Is Easy to Install On An Exi
Weight per unit	6.3 (lbs/each)
Product Category	Lighting

Features

dimensions	11.5 x 9.5 x 9.2
dimnable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
Light Source	LED - Static
lumens	10,000 LM,6000 LM
Power Source	Hardwired
Voltage Rating	120-277 V
Wattage	72

Material, Color, and Finish

Color	Silver
color rendering index (cri)	80
color temperature	Variable
Finish	Gloss
Style	Traditional

Dimensions and Weight

Height	9.2
Length	9.5
Width	11.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	BGR ALO SWW2 MVOLT PER DNA M2
extra long description	LITH BGR ALO SWW2 MVOLT PER DNA M2
Features	Contractor Select
Long Description	Barn lights, security lights, yard lights... call them what you will, but they are everywhere! Despite their utilitarian style and simplistic performance, they pose a significant opportunity for an upgrade to LED lighting. The Lithonia Lighting® BarnGuard LED security light has it all with its white light, high CRI, instant-on, and low energy consumption. Adjustable light output of up to 10,000 lumens and switchable color temperatures are standard features included. BarnGuard LED is easy to install on an exi
Product Type	Area Light

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00196182551260
Manufacturers Part Number	BGR ALO SWW2 MVOLT PER DNA M2
UPC	196182551260

Taxonomies, Classifications, and Categories

Category Description	LED CANOPY, PARKING, POLE MOUNTED & ROADWAY LIGHTING
Type	AREA LIGHT

Packaging

Carton	1
Package	2
Weight Per each	6.3

Uses, Certifications, and Standards

Application	Automotive & Parking, Education, Government, House of Worship, Manufacturing, Offices & Banks, Residential, Retail
environmental conditions	OUTDOOR
Mounting	Pole Mount, Surface
standard	C-UL-US DLC Premium