

Specifications

Eaton BJ44



Photo is representative

Eaton Crouse-Hinds series XJG bonding jumper, Rigid/IMC, 4" maximum conduit movement, Used with XJG44 HDG, 1-1/4" trade size

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series XJG bonding jumper
CATALOG NUMBER	BJ44
UPC	782274991894
PRODUCT LENGTH/DEPTH	24 in
PRODUCT HEIGHT	0.88 in
PRODUCT WIDTH	0.19 in
PRODUCT WEIGHT	1.4 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

CONDUIT TYPE	Rigid/IMC
TRADE SIZE	1-1/4"
CONDUIT MOVEMENT - MAX	4"
SPECIAL FEATURES	Used with XJG44 HDG

Resources

BROCHURES	Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure
CATALOGS	Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page
CERTIFICATION REPORTS	XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification
SPECIFICATIONS AND DATASHEETS	Expansion and Deflection Couplings Eaton Specification Sheet - BJ44

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton BJ44



Photo is representative

Eaton Crouse-Hinds series XJG bonding jumper, Rigid/IMC, 4" maximum conduit movement, Used with XJG44 HDG, 1-1/4" trade size

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series XJG bonding jumper
CATALOG NUMBER	BJ44
UPC	782274991894
PRODUCT LENGTH/DEPTH	24 in
PRODUCT HEIGHT	0.88 in
PRODUCT WIDTH	0.19 in
PRODUCT WEIGHT	1.4 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

CONDUIT TYPE	Rigid/IMC
TRADE SIZE	1-1/4"
CONDUIT MOVEMENT - MAX	4"
SPECIAL FEATURES	Used with XJG44 HDG

Resources

BROCHURES	Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure
CATALOGS	Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page
CERTIFICATION REPORTS	XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification
SPECIFICATIONS AND DATASHEETS	Expansion and Deflection Couplings Eaton Specification Sheet - BJ44

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

