



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR140 Type BR BRKR 40A/1 Pole 120/240V 10K

Eaton Corp

Catalog Number	BR140
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On Circuit Breaker, 40 A, 10 Kaic, Single-Pole, 120/240V, BR, #14-4 Awg Cu/Al, BR, Type BR Loadcenters
Weight per unit	0.3000 (lbs/each)
Product Category	1 Pole Standard Trip Plug-In

Features

amps	40
dimensions	3.0000 IN X 1.0000 IN X 3.0000 IN
interrupt rating	10 kAIC
pole #	Single
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	TYPE BR BRKR 40A/1 POLE 120/240V 10K
extra long description	ETN BR140 Type BR Breaker 40A/1 Pol
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 40 A, 10 kAIC, Single-pole, 120/240V, BR, #14-4 AWG Cu/Al, BR, Type BR Loadcenters
Product Type	Type BR Breaker 40A/1 Pole 120/240V 10K

Manufacturer Information

Brand	Eaton
GTIN	00786676362252
Manufacturers Part Number	BR140
UPC	786676362252

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Thermal magnetic circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.3

Uses, Certifications, and Standards

Application	Marine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: Cl and Hyper ConvergedOther
standard	UL 489,Federal Specifications Classification W-C375