



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BR1624B125 16/24C 125A 1PH MB Loadcenter

Eaton Corp

|                  |  |
|------------------|--|
| Catalog Number   | BR1624B125   |
| Manufacturer     | Eaton Corp   |
| Description      | BR Style Load Center, 16 Spaces, 24 Circuits, 125 A, 120/240 V Ac, #4 to 2/0 Awg Wire Size, Metallic Material, Aluminum Bus Material, 14.31 In Overall Length, 3.88 In Overall Width, 21 In Overall Height |
| Weight per unit  | 22.0 (lbs/each)  |
| Product Category | Single Phase Main Breaker Load   |

### Features

|                      |                                     |
|----------------------|-------------------------------------|
| amperage rating      | 125 VAC                             |
| Box Size             | 08447                               |
| cover                | Cover included                      |
| Cover Type           | Cover included                      |
| dimensions           | 5.1900 IN X 14.3100 IN X 18.7500 IN |
| main circuit breaker | CEMAT RSRT9 V7.0 OS SOFTWARE        |
| Number of Wires      | Three-wire                          |
| Phase                | 1 PH                                |
| used with            | Type BR 1-inch breakers             |

### Material, Color, and Finish

|                    |          |
|--------------------|----------|
| Enclosure Material | Metallic |
|--------------------|----------|

### Dimensions and Weight

|      |       |
|------|-------|
| Size | 08447 |
|------|-------|

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | 16/24C 125A 1PH MB LOADCENTER       |
| extra long description | ETN BR1624B125 BR style 1-inch load |

### Manufacturer Information

|      |                |
|------|----------------|
| GTIN | 00786676444408 |
| UPC  | 786676444408   |

### Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | LOADCENTERS & COVERS   |
| igcc                 | PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND |
| Type                 | Main circuit breaker   |
| unspsc code          | 39121101   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |    |
|-----------------|----|
| Carton          | 1  |
| Weight Per each | 22 |

## Uses, Certifications, and Standards

|                      |                             |
|----------------------|-----------------------------|
| Enclosure            | NEMA 1                      |
| Mounting<br>standard | Combination<br>UL 67; UL 50 |