



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR1624L125R 1PH/BR Loadcenter 125A Mlo 16/24 Cir. Al Bus Nema *Eaton Corp*

| | |
|------------------|--|
| Catalog Number | BR1624L125R |
| Manufacturer | Eaton Corp |
| Description | Eaton Eaton BR Main Lug Loadcenter, No Feed-Thru Lugs, Includes BREQS125 Hold-Down Screw, 125 A, B2R, Al, Nema 3R, Metallic, 10 Kaic, 24 Circuits, Twenty-Four Pole, 16 Spaces, Three-Wire, 1PH, Type BR 1-Inch Breakers, 120/240V, #6-2/0 Awg Cu/Al |
| Weight per unit | 23.0 (lbs/each) |
| Product Category | Single Phase Main Lug Load Cen |

Features

| | |
|------------------|-------------------------------------|
| amperage rating | 125 |
| Cover Type | Cover included |
| dimensions | 5.1900 IN X 14.3100 IN X 18.7500 IN |
| interrupt rating | 10 |
| number of spaces | 16 |
| Phase | 1 |
| Voltage Rating | 120/240V |

Dimensions and Weight

| | |
|--------|-------|
| Depth | 5.19 |
| Height | 18.75 |
| Size | B2r |
| Width | 14.31 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 1PH/BR LOADCENTER 125A MLO 16/24 CIR. AL BUS NEMA |
| extra long description | ETN BR1624L125R Eaton BR main lug I |
| Features | Specially designed for easy installation, Eaton's BR 1-inch load centers house the branch circuit breakers and the wiring required to distribute power to individual circuits. They serve as main breaker for service entrances or as main lug when adding circuits to existing service. The main breaker protects the entire panel and can be used as a service disconnect. The branch breakers protect the wires leading to individual electrical loads such as fixtures and outlets. |
| Long Description | Eaton Eaton BR main lug loadcenter, No feed-thru lugs, includes BREQS125 hold-down screw, 125 A, B2R, AI, NEMA 3R, Metallic, 10 kAIC, 24 Circuits, Twenty-four pole, 16 Spaces, Three-wire, 1ph, Type BR 1-inch breakers, 120/240V, #6-2/0 AWG Cu/Al |
| Product Type | Eaton BR Main Lug Loadcenter |
| Special Features | No feed-thru lugs, includes BREQS125 hold-down screw |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00786676446853 |
| Manufacturers Part Number | BR1624L125R |
| UPC | 786676446853 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | LOADCENTERS & COVERS |
| Type | Main lug loadcenter |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 23 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs |
| standard | UL 50, UL 67 |