



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR20I RCPT, Dup SB, Com GRD, 20A 125V, B/S, Iv *Hubbell Wiring Devices*

| | |
|------------------|---|
| Catalog Number | BR20I |
| Manufacturer | Hubbell Wiring Devices |
| Description | Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack. |
| Weight per unit | 0.0430 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|---------------------------|
| amperage rating | 20 |
| connection | Back and Side Wired |
| Current Rating | 20 |
| Dielectric Strength | Withstands 2,000V minimum |
| Material | Nylon |
| Number of Wires | 3-Wire |
| pallet quantity | 9000 |
| Phase | 1 |
| Poles | 2-Pole |
| Voltage Rating | 125 V |
| Wattage | 2500 |
| Wire Size | #12 to #10 |

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | 1.32 in x 0.83 in x 3.28 in |
|------|-----------------------------|

Descriptions

| | |
|------------------------|---|
| Description | RCPT, DUP SB, COM GRD, 20A 125V, B/S, IV |
| extra long description | HWK BR20I RCPT, DUP SB, COM GRD, 2 |
| Long Description | Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack. |
| Product Type | RCPT, Dup SB, Com GRD, 20A 125V, B/S, Iv |
| Special Features | Self Grounding |

Manufacturer Information

| | |
|---------------------------|--------------------------------|
| Brand | WIRING DEVICE-KELLEMS |
| GTIN | 00783585834887 |
| Manufacturers Part Number | BR20I |
| series | Commercial Specification Grade |
| UPC | 783585834887 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | Commercial receptacles |
| Type | Standard Duplex |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.043 |

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | Commercial Specification Grade |
| environmental conditions | Indoor Dry unless protected by additional means |
| Mounting | Screw Mount |
| nema rating | 5-20R |
| standard | Certified to CSA 22.2, No. 42; Fed. Spec. W-C-596; NEMA® WD-6 Compliant; UL Listed to UL498 File No. E2186 |